

## Features

- 2.5mm pitch
- Voltage Rating:250V
- Current Rating:3.0A
- Low Mating Force
- Reliable contact
- 3 Way Top Entry PCB Header

## RS PRO 2.5MM HEADER TOP ENTRY 3 WAY

RS Stock No.: 0147080



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Buy this product from [www.rspro.com](http://www.rspro.com)

- These Series Box-Type through hole Shrouded Headers are 2.5mm pitch, single row wire to board disconnect crimp style connectors. Available in Top Entry and Side Entry configurations. The wafer material of these Series Box-Type Shrouded Headers is Nylon 66 with a rating of UL 94V-0, Posts are Tin plated Brass for these Series Box-Type Shrouded Headers.
- Contact material is brass

## General Specifications

|                    |                   |
|--------------------|-------------------|
| Number of Contacts | 3                 |
| Number of Rows     | 1                 |
| Body Orientation   | Top Entry         |
| Dimensions(mm) A:  | 5                 |
| Dimensions(mm) B:  | 10                |
| Type               | Type 3            |
| Termination Method | Solder            |
| Contact Material   | Brass             |
| Contact Plating    | Tin plating       |
| Insulator          | Nylon 66, UL94V-0 |
| Colour             | White             |

## Electrical Specifications

|                       |                |
|-----------------------|----------------|
| Voltage Rating        | 250V AC,DC     |
| Current Rating        | 3A, AC, DC     |
| Insulation Resistance | 1000M ohm min  |
| Withstanding Voltage  | 800V AC/minute |

## Mechanical Specifications

|                 |                   |
|-----------------|-------------------|
| Mounting Type   | Through Hole      |
| Pitch           | 2.5 mm            |
| Square pin size | 0.64mm square pin |
| Pin height      | 3.4mm             |

## Operation Environment Specifications

|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 105°C |
|-----------------------|----------------|

## Approvals

|                           |                |
|---------------------------|----------------|
| Compliance/Certifications | RoHS Compliant |
| Declarations              | Reach          |

## Spec Drawings

