


Rittal TopTherm cooling units



TopTherm cooling units

- Energy-saving range of cooling units in the output range from 500 to 4000 W
- Savings of **up to 45%** energy consumption with the same cooling output (ideally 70% compared with a conventional Rittal TopTherm Plus cooling unit in field trials)

Eco-mode control

Intelligent, targeted use of energy thanks to the new eco-mode control from Rittal

- ❶ Cooling switches off: The interior fan only runs to ensure air circulation inside the enclosure.
- ❷ The interior fan is switched off.
- ❸ The interior fan is switched on for 30 seconds every 10 minutes to briefly blend the air.
- ❹ The interior fan is switched back on.

Generation “Blue e”

Save energy permanently with Rittal cooling units.



TopTherm cooling units

Roof-mounted/wall-mounted

Roof-mounted cooling units

With e-Comfort controller

Useful cooling output	Dimensions W x H x D mm	Voltage V, Hz	Model No. SK
500 W	597 x 417 x 380	230, 50/60	3382.500
		115, 50/60	3382.510
750 W	597 x 417 x 380	230, 50/60	3359.500
		115, 50/60	3359.510
		400, 2~, 50/60	3359.540
1000 W	597 x 417 x 475	230, 50/60	3383.500
		115, 50/60	3383.510
		400, 2~, 50/60	3383.540
1500 W	597 x 417 x 475	230, 50/60	3384.500
		115, 50/60	3384.510
		400, 2~, 50/60	3384.540
2000 W	597 x 417 x 475	230, 50/60	3385.500
		115, 50/60	3385.510
		400, 2~, 50/60	3385.540
3000 W	796 x 470 x 580	400, 3~, 50	3386.540
		460, 3~, 60	
4000 W	796 x 470 x 580	400, 3~, 50	3387.540
		460, 3~, 60	

Cooling unit versions in stainless steel may be found on the Internet.



Wall-mounted cooling units

With e-Comfort controller

Useful cooling output	Dimensions W x H x D mm	Voltage V, Hz	Model No. SK
500 W	280 x 550 x 200	230, 50/60	3303.500
		115, 50/60	3303.510
750 W	280 x 550 x 280	230, 50/60	3361.500
		115, 50/60	3361.510
		400, 2~, 50/60	3361.540
1000 W	400 x 950 x 260	230, 50/60	3304.500
		115, 50/60	3304.510
		400, 3~, 50 460, 3~, 60	3304.540
1500 W	400 x 950 x 260	230, 50/60	3305.500
		115, 50/60	3305.510
		400, 3~, 50 460, 3~, 60	3305.540
1500 W	450 x 1590 x 205	230, 50/60	3366.500
		115, 50/60	3366.510
		400, 3~, 50 460, 3~, 60	3366.540
2000 W	400 x 1580 x 295	230, 50/60	3328.500
		115, 50/60	3328.510
		400, 3~, 50 460, 3~, 60	3328.540
2500 W	400 x 1580 x 295	230, 50/60	3329.500
		115, 50/60	3329.510
		400, 3~, 50 460, 3~, 60	3329.540
4000 W	500 x 1580 x 340	400, 3~, 50	3332.540
		460, 3~, 60	

Cooling unit versions in stainless steel, Nema 4X and with climate control doors may be found on the Internet.

