
Geberit Mapress Stainless Steel adaptor with female thread



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5
- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material	CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	Rp "	L cm	Z cm
33010	10 / 15	12	1/2	3.4	0.4
31801	12 / 10	15	3/8	3.5	0.5
31802	12 / 15	15	1/2	3.7	0.4
31823	12 / 20	15	3/4	3.8	0.3

GEBERIT

Art. no.	DN	d, ø mm	Rp "	L cm	Z cm
31803	15	18	1/2	3.7	0.4
31804	15 / 20	18	3/4	3.8	0.3
31805	20 / 15	22	1/2	3.6	0.2
31806	20	22	3/4	3.9	0.3
31824	20 / 25	22	1	4.2	0.4
31807	25 / 15	28	1/2	3.8	0.2
31819	25 / 20	28	3/4	3.9	0.3
31809	25	28	1	4.4	0.4
31825	25 / 32	28	1 1/4	4.6	0.4
31820	32 / 25	35	1	4.5	0.2
31811	32	35	1 1/4	4.9	0.4
31826	32 / 40	35	1 1/2	4.9	0.4
31821	40 / 32	42	1 1/4	5.1	0.2

Art. no.	DN	d, ø mm	Rp "	L cm	Z cm
31814	40	42	1 1/2	5.3	0.4
31822	50 / 40	54	1 1/2	7.7	2.1
31818	50	54	2	6.2	0.4