




TE Internal #: 1971920-2

TE Internal Description: SOCKET KITS, PV4 PANEL MOUNTED CONNECTOR

SOLARLOK PV4-S DC Crimp Connectors

[View on TE.com >](#)



All SOLARLOK PV4-S DC Crimp Connectors (12)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # CAT-SAFE-TE
Solarlok SAFE-TE Connectors




TE Part # 1971920-1
SOCKET KITS, PV4 PANEL MOUNTED CONNECTOR


Customers Also Bought




TE Part #2-1625885-7
1W SM M/OX 5% 180R




TE Part #440055-4
2.0MM,HDR,4POS,R/A




TE Part #2213936-3
SMT TB SCREW RECEPTACLE, 3.5 MM, 3 POS




TE Part #4-1393789-7
V23079D2008B301




TE Part #796637-2
2POS 5.08MM CE VRT HDR,TRM BLK




TE Part #1623488-1
CRG1206 1% 330R




TE Part #2027395-5
T9VV1K15-12S



TE Part #1SNG607013R0000
EP-LN-M32-LGR-A



TE Part #2-1462039-6
IM21GR=IM RELAY 50mW 3V



TE Part #1625862-4
RH73 2A 50G 30% 1000PPM 1K RL

Documents

Product Drawings
SOCKET KITS, PV4 PANEL MOUNTED CONNECTOR

English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_1971920-2_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1971920-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1971920-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOLARLOK PV4-PM CONNECTOR 1000V DC](#)

English

[SOLARLOK PV4-S DC CRIMP CONNECTORS](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[TUV Certificate](#)

English

[TUV Certificate](#)

English