

# US-WMT (30X4) VT - Cable marker



0829311

<https://www.phoenixcontact.com/gb/products/0829311>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Card, violet, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, cable diameter range: 1.5 ... 14 mm, mounting type: slide-on, Number of individual labels: 42, text field height: 4 mm, text field width: 30 mm

## Your advantages

- The US-WMT ... UniSheet labeling range includes markers for conductor marking with marking collars from the PATG/PATO ... system
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0829311             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | BG2219              |
| Product key                          | BG2219              |
| Catalog page                         | Page 221 (C-3-2017) |
| GTIN                                 | 4046356612784       |
| Weight per piece (including packing) | 12.36 g             |
| Weight per piece (excluding packing) | 12.36 g             |
| Customs tariff number                | 39204910            |
| Country of origin                    | DE                  |

# US-WMT (30X4) VT - Cable marker

0829311

<https://www.phoenixcontact.com/gb/products/0829311>



## Technical data

### Product properties

| Product type                        | Conductor marking |
|-------------------------------------|-------------------|
| Marking                             |                   |
| Number of individual labels         | 42                |
| Number of individual labels per row | 14                |

### Dimensions

|                   |         |
|-------------------|---------|
| Width             | 4.3 mm  |
| Depth             | 0.5 mm  |
| Length            | 30 mm   |
| Material strength | 0.50 mm |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 30 mm |
| Text field height | 4 mm  |

### Material specifications

|                                        |                   |
|----------------------------------------|-------------------|
| Color                                  | violet (RAL 4005) |
| Material                               | PVC               |
| Flammability rating according to UL 94 | V0                |
| Components                             | Silicone-free     |

### Cable/line

|                         |                  |
|-------------------------|------------------|
| External cable diameter | 1.5 mm ... 14 mm |
|-------------------------|------------------|

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Wipe resistance of inscriptions

|                                                 |                                                |
|-------------------------------------------------|------------------------------------------------|
| Specification                                   | DIN EN 61010-1 (VDE 0411-1):2011-07            |
|                                                 | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                  | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed                                    |

# US-WMT (30X4) VT - Cable marker



0829311

<https://www.phoenixcontact.com/gb/products/0829311>

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                               |
|---------------|-------------------------------|
| Specification | DIN 50018:2013-05 (following) |
| Result        | Test passed                   |
| Climate level | AHT 1.0 S                     |
| Cycles        | 2                             |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |

## Ambient conditions

|                                                     |                                                                                                                     |
|-----------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -30 °C ... 80 °C                                                                                                    |
| Recommended storage conditions                      | 10 ... 30 °C / 40 ... 70 % relative humidity. Storage in the original packaging is recommended prior to processing. |
| Recommended ambient temperature (storage/transport) | 10 °C ... 30 °C                                                                                                     |
| Recommended humidity (storage/transport)            | 40 % ... 70 %                                                                                                       |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

# US-WMT (30X4) VT - Cable marker



0829311

<https://www.phoenixcontact.com/gb/products/0829311>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281106 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# US-WMT (30X4) VT - Cable marker



0829311  
<https://www.phoenixcontact.com/gb/products/0829311>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)