

18V Brushless Combi Drill LXT

DHP481RTJ

Model DHP481 is a supreme class cordless hammer-driver drill powered by 18V Li-ion battery

Supplied with Type 2 Makpac Case



TECHNICAL SPECIFICATIONS

Chuck Capacity	1.5 - 13 mm
No Load Speed (Hi)	0 - 2100 rpm
No Load Speed (Lo)	0 - 550 rpm
Blows per Minute (Hi) - ipm	0 - 31,500 ipm
Blows per Minute (Lo) - ipm	0 - 8,250 ipm
Voltage	18 v
Max. in wood	76 mm
Max. in masonry	16 mm
Max. in steel	13 mm
Torque Settings	21 + drill
Battery Type	Lithium-ion
Vibration K factor	1.5 m/sec ²
Battery Quantity (5.0ah)	2
Max. Fastening Torque (Soft Joint)	60 Nm
Max. Fastening Torque (Hard Joint)	115 Nm
Vibration: Impact drilling into concrete	6.5 m/sec ²
Vibration: Drilling into metal	2.5 m/sec ²
Weight (with batteries)	2.7 - 3.0 kg

USER BENEFITS

- Forward / reverse rotation
- Single sleeve keyless chuck allows for easy bit installation/removal by one hand.
- Electric brake
- Twin LED job light with afterglow.
- 2 mechanical gears.
- Battery fuel gauge
- Variable speed control by trigger
- Best possible ergonomic handle for drill-driver applications.
- Compact overall length.

Link to product - www.makitauk.com



RELATED PRODUCTS

(Recom

STANDARD ACCESSORIES

197282-4

Battery BL1850B 18v Li-ion



821550-0

MAKPAC CONNECTOR CASE (TYPE



837916-4

MAKPAC INLAY FOT TYPE 2 CASE



DC18RC

DC18RC COMPACT CHARGER



OTHER