
Your Expert Partner for **Human Machine Interfaces**

Rotary switching element

Distribution by
Rs-online

704.8A639



https://rs-online.eao.com/component/704.8A639...

Your product:



704.8A639
Rotary switching element

ELECTRICAL CHARACTERISTICS

Operating voltage:	20
Rated impulse withstand voltage Uimp:	4 kV
Switching rating:	440 V AC @ 10 A

MECHANICAL CHARACTERISTICS

Terminal:	Screw terminal
Contact material:	Gold
Switching system:	Slow-make switching element
Switching positions:	12 positions
Tightening torque:	Fixing nut max. 0.25 Nm
Wire cross section:	Single-core or stranded wire 2 x 1.5 mm^2 (2 x AWG 14) Flexible wire 2 x 1.5 mm^2 (2 x AWG 16)
Weight:	0.082 kg

AMBIENT CONDITION

Operating temperature:	Ambient Temperatures of Stages, open at 100 % Iu / Ith: 55 °C during 24 h with peaks up to 60 °C, enclosed at 100 % Ithe: 35 °C during 24 h with peaks up to 40 °C

CERTIFICATE

REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER

Short Description: Rotary switching element, Slow-make switching element, 440 V AC @ 10 A, Gold, Screw terminal

Wiring diagrams:

