#### Ordering information

# PCA600F

A 600



①Series name ②Single output ③Output wattage ④Universal input

⑤Output voltage

(B) Optional \*6
 P2: Bus Bar Style
 TP2: Terminal Block Style

For details of TP2, refer to instruction manual 7.1.

\*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

MODEL	PCA600F-5-P2	PCA600F-12-P2	PCA600F-15-P2	PCA600F-24-P2
MAX OUTPUT WATTAGE[W]	600	636	645	648
DC OUTPUT	5V 120A	12V 53A	15V 43A	24V 27A

# **SPECIFICATIONS**

	MODEL			PCA600F-5-P2	PCA600F-12-P2	PCA600F-15-P2	PCA600F-24-P2		
	VOLTAGE[VAC]			85 - 264 1 φ (Output de	rating is required at less the	an 90V. Refer to instruction m	nanual 5.2.)		
INPUT	CUDDENTIAL		ACIN 100V	7.3typ					
	CURRENT[A]		ACIN 230V	3.2typ					
	FREQUENCY[H	lz]	•	50/60 (45 - 66)					
	_	1001140014	(lo=50%)	90typ	91typ	91typ	91typ		
	EFFICIENCY[%]	ACIN 100V	(lo=100%)	89typ	90typ	90typ	91typ		
		ACIN 230V	(lo=50%)	92typ	92typ	92typ	93typ		
			(lo=100%)	91typ	92typ	92typ	93typ		
			ACIN 100V	0.98typ (lo=100%)	, ,,	1 21	, , , ,		
	POWER FACTOR		ACIN 230V	0.95typ (Io=100%)					
	INRUSH CURRENT[A]  ACIN 100V*1 ACIN 230V*1 LEAKAGE CURRENT[MA]		ACIN 100V*1	, ,	rimary inrush current / Seco	ondary inrush current) (More t	than 3 sec. to re-start)		
			ACIN 230V*1	40/40 typ (lo=100%) (P	rimary inrush current / Seco	ondary inrush current) (More t	than 3 sec. to re-start)		
				0.5max (ACIN 240V 60Hz, Io=100%, According to IEC60601-1)					
	VOLTAGE[V]		5	12	15	24			
	CURRENT[A]		120	53	43	27			
	LINE REGULAT	TION[mV1		20max	48max	60max	96max		
ŀ	LOAD REGULA		1	40max	100max	120max	150max		
			0 to +50°C *2*3	160max	240max	240max	240max		
	RIPPLE[mVp-p	]	-20 to 0°C *2	280max	320max	320max	320max		
			0 to +50°C *2*3	240max	300max	300max	300max		
ОИТРИТ	RIPPLE NOISE	[mVp-p]	-20 to 0°C *2	320max	360max	360max	360max		
		-	0 to +50°C *3	50max	120max	150max	240max		
	TEMPERATURE REGU	LATION[mV]	-20 to +50°C *3	75max	180max	180max	290max		
	DRIFT[mV]		*4	20max	48max	60max	96max		
	START-UP TIME[ms]		400typ (ACIN 100/230V Io=100%)						
	HOLD-UP TIME[ms]		20typ (ACIN 230V Io=80%) / 16typ (ACIN 230V Io=100%)						
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		3.00 to 6.00	7.20 to 14.40	9.00 to 18.00	14.40 to 28.80			
	OUTPUT VOLTAGE SETTING[V]		5.00 to 5.15	12.00 to 12.48	15.00 to 15.60	24.00 to 24.96			
	OVERCURRENT PROTECTION			ing (Recovers automatically		1 - 1100 10 - 1100			
	OVERVOLTAGE PROTECTION[V]		6.25 to 7.00	15.00 to 16.80	18.75 to 21.00	30.00 to 33.60			
PROTECTION	REMOTE SENSING			Provided   15.00 to 10.00   10.73 to 21.00   00.00 to 00.00					
CIRCUIT AND	REMOTE ON/OFF (RC)			Provided					
OTHERS	DC OK LAMP			LED (Blue)					
	ALARM LAMP			LED (Orange)					
	COMMUNICATION FUNCTION			Provided (Extended UART)					
	INPUT-OUTPUT			AC4,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At Room Temperature) 2MOPP					
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M $\Omega$ min (At Room Temperature) 1MOPP						
ISOLATION	OUTPUT-FG		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At Room Temperature)						
	OUTPUT - AUX · RC · PG · INFO · MS · ADDRO · ADDR1 · ADDR2		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At Room Temperature)						
	OPERATING TEMP.,HUMIDITY.AND ALTITUDE			-20 to +70°C, 20 - 90%RH (Non condensing)					
	STORAGE TEMP.,HUMIDITY.AND ALTITUDE		-20 to +75°C, 20 - 90%RH (Non condensing)						
ENVIRONMENT	VIBRATION			10 - 55Hz 19.6m/s² (2G) 3minutes period, 60minutes each along X, Y and Z axis					
	IMPACT			196.1m/s² (20G) 11ms, once each X, Y and Z axis					
SAFETY	AGENCY APPROVALS			UL60950-1, C-UL (CSA60950-1), EN60950-1, ANSI/AAMI ES60601-1, EN60601-1 3rd, Complies with IEC60601-1-2 4th Ed.					
AND NOISE	CONDUCTED NOISE			Complies with FCC Part15 classB, VCCI-B, CISPR32-B, EN55011-B, EN55032-B					
REGULATIONS				Complies with IEC61000-3-2 (class A)					
	TATINIONIC AT	LINDAID	***************************************	Complies with IECO100	0 0 2 (Ulass A)				





#### **SPECIFICATIONS**

OTHERS	CASE SIZE/WEIGHT	89×41×152mm [3.50×1.61×5.98 inches] (without terminal block and screw) (W×H×D) / 840g max		
	COOLING METHOD	Forced cooling (internal fan)		

- The value is primary surge. The current of input surge to a built-in EMI/EMS Filter(0.2ms or
- \*2 Measured by 20MHz oscilloscope or Ripple-Noise meter (equivalent to KEISOKU-GIKEN:RM103).
- \*3 5V output product, the maximum temperature of 40°C.


- Drift is the change in DC output for an eight hours period after a half-hour warm-up at 25°C.
- \*5 Please contact us about another class.
- \*6 The listed options may affect the published standard specifications. Please contact us for detailed product specifications and safety approvals.
- A sound may occur from power supply at pulse loading.

#### **Features**

- · Low profile (41mm, 1.61 inch = meet to 1U height)
- · Universal input 85 264VAC (Refer to item 5.2,in case of using at 85 - 90VAC)
- · For medical electric equipment (ANSI/AAMI ES60601-1, EN60601-1 3rd, IEC60601-1-2 4th Ed.)
- ·With AUX output
- · Constant current regulation

- · Output voltage can be varied to near 0V (Refer to item 3.6)
- · With various alarms
- · Parallel operation possible
- · Monitoring function by communication and various setting values can be changed (Refer to item 3.11)


## **Block diagram**








## **External view**

# <PCA600F- -P2 (Bus Bar Style) >











- % Tolerance :  $\pm 1$  [ $\pm 0.04$ ]
- Weight: 840g max
- $\frak{W}$  PCB Material / thickness : FR-4 / 1.6mm [0.06]
- Chassis Material : Aluminum
  Fan cover Material : PBT
  Dimensions in mm, [ ]=inches
  Mounting torque : 1.2N·m max
- ※ Screw tightening torque: 1.6N⋅m max
- \* Please connect safety ground to FG terminal on the unit.




# **External view**


# <PCA600F- TP2 (Terminal Block Style) >











※ PCB Material / thickness: FR-4 / 1.6mm [0.06]

\* Chassis Material : Aluminum ※ Fan cover Material : PBT \* Dimensions in mm, [ ]=inches

 Mounting torque: 1.2N·m max ※ Screw tightening torque: M4 1.6N⋅m max

M5 2.5N·m max

\* Please connect safety ground to FG terminal on the unit.

