



INDICATOR LIGHT, 22MM, ROUND, METAL, SHINY, WHITE, SMOOTH LENS, WITH HOLDER, LED MODULE, WITH INTEGRATED LED 24V AC/DC, SCREW TERMINAL

Figure similar

product brand name		SIRIUS ACT
Product designation		Commanding and signaling devices
Design of the product		Pilot Light
<b>Manufacturer article number</b>		
<ul style="list-style-type: none"> <li>• of supplied LED module</li> </ul>		<a href="#">3SU1401-1BB60-1AA0</a>
<ul style="list-style-type: none"> <li>• of the supplied holder</li> </ul>		<a href="#">3SU1550-0AA10-0AA0</a>
<ul style="list-style-type: none"> <li>• of supplied repeater</li> </ul>		<a href="#">3SU1052-6AA60-0AA0</a>

#### Actuator:

<b>Product expansion optional Light source</b>		Yes
<b>Color</b>		
<ul style="list-style-type: none"> <li>• of the actuating element</li> </ul>		White
<b>Material of the actuating element</b>		plastic
<b>Shape of the actuating element</b>		round
<b>Outer diameter of the actuating element</b>	mm	29.45

#### Front ring:

<b>Product component front ring</b>		No
-------------------------------------	--	----

#### Holder:

<b>Material of the holder</b>		Metal
-------------------------------	--	-------

#### Display:

<b>Number of LED modules</b>		1
------------------------------	--	---

#### General technical data:

<b>Product component</b>		
<ul style="list-style-type: none"> <li>• Light source</li> </ul>		Yes

<b>Insulation voltage</b>		
• Rated value	V	320
<b>Type of voltage</b>		
• of the operating voltage		AC/DC
<b>Degree of pollution</b>		3
<b>Vibration resistance</b>		
• acc. to IEC 60068-2-6		10 ... 500 Hz: 5g
<b>Surge voltage resistance Rated value</b>	kV	4
<b>Protection class IP</b>		
• of the terminal		IP20
<b>Equipment marking</b>		
• acc. to DIN EN 61346-2		P
• acc. to DIN EN 81346-2		P
<b>Operating voltage</b>		
• Rated value	V	24
<b>Relative positive tolerance of the operating voltage</b>	%	20
<b>Relative negative tolerance of the operating voltage</b>	%	20

#### Auxiliary circuit:

<b>Number of NC contacts</b>		
• for auxiliary contacts		0
<b>Number of NO contacts</b>		
• for auxiliary contacts		0
<b>Number of CO contacts</b>		
• for auxiliary contacts		0

#### Connections/ Terminals:

<b>Type of electrical connection</b>		
• of modules and accessories		Screw-type terminal
<b>Type of connectable conductor cross-section</b>		
• solid with core end processing		2x (0.5 ... 0.75 mm <sup>2</sup> )
• solid without core end processing		2x (1.0 ... 1.5 mm <sup>2</sup> )
• finely stranded with core end processing		2x (0.5 ... 1.5 mm <sup>2</sup> )
• finely stranded without core end processing		2x (1,0 ... 1,5 mm <sup>2</sup> )
• for AWG conductors		2x (18 ... 14)
<b>Tightening torque</b>		
• with screw-type terminals	N·m	0.8 ... 0.9

#### Lamp:

<b>Type of light source</b>		LED
<b>Color of the light source</b>		white

#### Ambient conditions:

<b>Ambient temperature</b>		
• during operation	°C	-25 ... +70

- during storage

°C	-40 ... +80
----	-------------

**Installation/ mounting/ dimensions:**

<b>Mounting type</b>		front panel mounting
• of modules and accessories		Front plate mounting
<b>Height</b>	mm	40
<b>Width</b>	mm	30
<b>Shape of the installation opening</b>		round
<b>Mounting diameter</b>	mm	22

**Certificates/ approvals:**

**Further information**

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3SU11526AA601AA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**


<http://support.automation.siemens.com/WW/view/en/3SU11526AA601AA0/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=3SU11526AA601AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3SU11526AA601AA0&lang=en)



**-P**  
24 V AC/DC



last modified:

09.03.2015