



2 YEARS
MANUFACTURER
GUARANTEE

200
LUMEN

12h
MAX.

USB RECHARGEABLE

RECHARGEABLE

Product number 1175590110
EAN 4007123690466

TECHNICAL DATA

Luminous flux	200 lm	Number of batteries	1
Colour temperature	6500 K	Battery type	Built-in battery pack
Battery capacity	0.45 Ah	Battery technology	Lithium polymer
Battery voltage	3.7 V	Protection class	III
Light duration max.	12 h	Degree of protection (IP)	IP20
Battery charging time approx.	2 h	Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	10	Weight of product (including packaging)	0.09 kg
Weight of product (without packaging)	0.04 kg	Dimension LxWxH (incl. packing)	2.5 cm x 5.6 cm x 20.5 cm
Dimension LxWxH (without packing)	1.2 cm x 2.5 cm x 12.3 cm		