



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:26 (UTC)



22226EAE4

Spherical Roller Bearings

Boundary Dimensions

d	130	mm	Bore diameter
D	230	mm	Outside diameter
B	64	mm	Width
r (min.)	3	mm	Chamfer dimension

Basic Load Ratings

Cr	820000	N	Basic dynamic load rating
C0r	940000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	2800	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	2600	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	2200	min-1	Grease lubrication
Oil (Oil-bath)	2600	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	144	mm	Diameter of shaft abutment
da (max.)	152	mm	Diameter of shaft abutment
Da (min.)	204	mm	Diameter of housing abutment
Da (max.)	216	mm	Diameter of housing abutment
ra (max.)	2.5	mm	Radius of shaft or housing fillet

Calculation factors

e	0.26	Constant
Y2	3.8	Axial load Factors
Y3	2.6	Axial load Factors
Y0	2.5	Axial load Factors

Mass

Mass approx.	11	kg	Mass approx.
--------------	----	----	--------------

