
GSB 21-2 RE Professional



Impact drill

GSB 21-2 RE Professional

The most powerful tool in its class - for the toughest applications

- **Bosch high-performance motor (1100 W) with high torque for the most heavy-duty applications with large diameters (drilling, working with core cutters and holesaws), screwdriving and stirring**
- **Sturdy metal gear housing for long lifetime**
- **Anti-rotation mechanical overload clutch for high level of work safety, even in the toughest applications**



- Single-sleeve keyless chuck with Auto-Lock for quick accessory changes with only one hand

- New safety handle with innovative attachment and softgrip for a secure hold on the machine
- Speed preselection with setting wheel for precise working
- Rotating brush plate for constant power in reverse and forward rotation
- Softgrip on main handle for a secure hold
- Ball grommet for high movement radius and for preventing cable breaks
- Spindle collar diameter of 43 mm (European standard) – can be used in drill stands

Part no. 0 601 19C 560

- Keyless chuck 13 mm (2 608 572 150)
- Auxiliary handle (2 605 025 193)
- Depth stop 210 mm (1 613 001 010)
- Carrying case (2 605 438 524)

Voltage, electrical	110 V
---------------------	-------

Part no. 0 601 19C 570

- Keyless chuck 13 mm (2 608 572 150)
- Auxiliary handle (2 605 025 193)
- Depth stop 210 mm (1 613 001 010)
- Carrying case (2 605 438 524)

Voltage, electrical	230 V
---------------------	-------

Technical data

Rated power input	1.100 W
No-load speed	0 – 900 / 3.000 rpm
Power output	630 W
Weight without cable	2,9 kg
Rated speed	0 – 580 / 1.900 rpm

Rated torque	9,6 / 3,2 Nm
Drill spindle connecting thread	1/2" – 20 UNF
Chuck capacity	1,5 – 13 mm
Impact rate at no-load speed	0 – 15.300 / 51.000 bpm
Max. torque	40,0 / 14,5 Nm

Drilling range

Drilling dia. in concrete	22 / 13 mm
Drilling dia. in wood	40 / 25 mm
Drilling dia. in steel	16 / 8 mm
Drilling dia. in masonry	24 / 16 mm

Functions

- Multiple gears
- Forward/reverse operation
- Electronic
- Auto-Lock
- Softgrip
- Overload clutch

Noise/vibration information

Show values

Measured values determined according to EN 60745.

Total vibration values (vector sum of three directions)

Drilling in metal

Vibration emission value ah	5,6 m/s ²
Uncertainty K	1,5 m/s ²

Impact drilling in concrete

Vibration emission value ah	14,6 m/s ²
Uncertainty K	1,8 m/s ²

Screwdriving

Vibration emission value ah	2,5 m/s ²
-----------------------------	----------------------

Uncertainty K	1,5 m/s ²
---------------	----------------------

Thread-cutting

Vibration emission value ah	2,5 m/s ²
-----------------------------	----------------------

Uncertainty K	1,5 m/s ²
---------------	----------------------

The A-rated noise level of the power tool is typically as follows: Sound pressure level 95 dB(A); Sound power level 106 dB(A). Uncertainty K= 3 dB.

