

Features

- Nylon 6/6
- High Quality
- 25 x 100mmx2.5mm,
25 x 200mmx3.2mm.
Natural Colour
- Easy to use
- Available in a range of
colours

RS PRO Cable Ties Value Pack

RS Stock No.: 0267992



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Nylon Non-Releasable Cable Ties. Their primary purpose is to aid clean installations by holding cables together or in a specific location. They however have various other uses such as hanging or storing parts ready to paint. RS PRO Nylon Non-Releasable Cable Ties are made from nylon, easy to use and are an essential item for any toolbox.

General Specifications

Type	Non-releasable
Colour	Natural
Material	Nylon 6/6
Application	Bundling wire together, Suitable for use in electrical and electronic servicing, maintenance, mechanical and automotive applications.
Resistant To	Ultraviolet Resistance
UV Resistant	No
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+85°C
Fire Behaviour	Flame Retardant
Quantity	50

Mechanical Specifications

Size	100mm x 2.5mm and 200mm x 3.2mm
Tensile Strength	See below chart


Approvals

Standards Met

UL94V-2

Similar Products

Dimensions



RS Article	Colour	Length (mm)	Width (mm)	Quantity	Min. Tensile Strength (Kg)	Max Bundle Dia. (mm)
178-462	Natural	100	2.5	100	8	22
233-499	Black	100	2.5	100	8	22
492-0447	Natural	100	2.5	1000	8	22
233-455	Black	100	2.5	1000	8	22
178-478	Natural	150	3.6	100	18	36
233-465	Black	150	3.6	100	18	36
492-0453	Natural	150	3.6	1000	18	36
233-500	Black	150	3.6	1000	18	36
178-484	Natural	190	4.8	100	22	49
233-461	Black	190	4.8	100	22	49
492-0469	Natural	190	4.8	1000	22	49
233-506	Black	190	4.8	1000	22	49

RS Article	Colour	Length (mm)	Width (mm)	Quantity	Min. Tensile Strength (Kg)	Max Bundle Dia. (mm)
489-2140	Natural	203	4.6	100	22	52
233-471	Black	203	4.6	100	22	52
178-490	Natural	292	3.6	100	18	82
233-477	Black	292	3.6	100	18	82
489-2156	Natural	300	4.8	100	22	83
233-487	Black	300	4.8	100	22	83
178-507	Natural	368	4.8	100	22	105
233-483	Black	368	4.8	100	22	105
233-493	Black	380	7.6	100	55	105

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories