



Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLA
Nominal height	1500 mm
Nominal width	1250 mm
Nominal depth	320 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel

Complementary

Body type	Sealed top and bottom part assembled with side parts
Door type	Transparent front
Number of doors	2 door(s)
Door opening side	Right and left (120 °)
Lock type	4 points lock, 5 mm double-bar
Accessibility for operation	Front Rear
Removable parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208 UL 508 A
NEMA degree of protection	NEMA 1 NEMA 2 NEMA 12 NEMA 13
Product certifications	DNV Marine[RETURN]UL/cUL listed[RETURN]Veritas
Electrical insulation class	Class II

Environment

IP degree of protection	IP65 conforming to IEC 60529 (completely sealed)
IK degree of protection	IK08 conforming to IEC 62262 (glazed door)
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-35...90 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations