




QSFP/QSFP+

TE Internal #: 1-1761987-8
QSFP+, Connector, .8mm [.032in] Centerline, Signal, Operating
Temperature Range -55 – 105 °C [-67 – 221 °F], 38 Position
[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages



Form Factor: **QSFP+**
Pluggable I/O Product Type: **Connector**
Centerline (Pitch): **.8 mm [.032 in]**
Sealable: **No**
Circuit Application: **Signal**

Features

Product Type Features

Form Factor	QSFP+
Pluggable I/O Product Type	Connector
Sealable	No

Configuration Features

Number of Positions	38
---------------------	----

Contact Features

Contact Current Rating (Max)	.5 A
Contact Mating Area Plating Material	Gold (Au)
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.38 µm[15 µin]

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Centerline (Pitch)	.8 mm[.032 in]
--------------------	----------------

Dimensions

PCB Thickness (Recommended)	1.45 mm[.057 in]
-----------------------------	------------------

Usage Conditions

--	--



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tape
------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2202165-5
QSFP TO QSFP, 26AWG, FDR, 5.0 METER



TE Part # 2202165-4
QSFP TO QSFP, 26AWG, FDR, 4.0 METER



TE Part # 2053453-5
C/A, QSFP TO 4XSFP+, 4.0M



TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP



TE Part # 2821033-8
QSFP TO [4]SFP+, 28G, 1M, 33AWG



TE Part # 2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part # CAT-C11-H501142
QSFP to QSFP I/O Cable Assembly: 33 AWG



TE Part # 1-2053638-6
C/A, QSFP, 0.5M, P1-P2, UNEQUALIZED




TE Part # CAT-C11-H50111
QSFP-Four SFP+ I/O Cable Assembly 30 AWG


Also in the Series | [QSFP/QSFP+](#)



Pluggable I/O Cable Assemblies(13)



Pluggable IO Connectors & Cages(154)



QSFP, QSFP+ & zQSFP+(154)


Customers Also Bought



TE Part #1721261-5
OJE-SS-112LMH2



TE Part #1721260-5
OJ-SS-112LMH2



TE Part #7-6450831-5
MBXL R/A HDR12S+2P+12LP



TE Part #1954041-2
POWER ARCH PIN CONTACT .153 INCH DIA.





TE Part #2173132-1
ELCON MINI 4P VERT HEADER,
UNSHIELDED,SOL



TE Part #1-1721539-7
OJE-SS-112HM2.000T0



TE Part #1888617-1
Cage Assy, QSFP, Through Bezel

TE Part #2373238-1
487-322-01

TE Part #3-6450834-1
MBXLE R/A HDR 8P+20S

TE Part #1878032-7
487-322-00

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1-1761987-8_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1761987-8_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-1761987-8_A.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English