



SLIM DRUM DESIGN FOR POWERFUL AIRFLOW



ADJUSTABLE TILTING FAN HEAD FOR DYNAMIC AIR CIRCULATION



3 SETTINGS FOR VARIABLE FAN SPEED



155CM POWER CABLE CAN BE STOWED WHEN NOT IN USE

ITEM. 05613

SIP 20" HEAVY-DUTY FLOOR FAN

POWERFUL FLOOR FAN FOR EFFECTIVE AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 20" Heavy-Duty Floor Fan** uses a 5-blade design to deliver powerful airflow to help cool spaces and circulate air in a variety of indoor environments. Fixed in a slim drum casing and mounted on a sturdy steel frame, the fan can be tilted on it's vertical axis to adjust the airflow and provide outstanding cooling and air circulation coverage.

Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 5-blade fan is powered from a 111w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

3 settings for variable fan speed:

- **Low:** 850rpm
- **Medium:** 1100rpm
- **High:** 1350rpm

✓ TILTING FAN HEAD

The adjustable fan head tilts on it's vertical axis for dynamic circulation of air.

A robust balanced steel frame maintains fan stability when in use.

THIS PRODUCT COMES WITH AN SIP 2-YEAR SILVER WARRANTY*

FIND OUT MORE AT SIP-GROUP.COM/WARRANTY



ITEM. 05613

SIP 20" HEAVY-DUTY FLOOR FAN

FEATURES & BENEFITS CONT.

✓ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.

APPLICATIONS & USES

DELIVERS POWERFUL VARIABLE SPEED
AIR CIRCULATION TO INDOOR SPACES

PERFECT FOR INDOOR AREAS SUCH AS OFFICES,
WORKSHOPS OR DOMESTIC USES

ITEM NO.	05613		
INPUT SUPPLY	230v (13A)		
MOTOR POWER	111w (0.14hp)		
POWER CABLE	155cm		
FAN DIAMETER	Ø 20" (508mm)		
SPEED SETTINGS	3 speed settings		
	Low	Medium	High
	850rpm	1100rpm	1350rpm
NOISE LEVEL	75dB(A)		
NET WEIGHT	5.69kg		
GROSS WEIGHT	7kg		
PRODUCT DIMENSIONS	525(H) x 605(W) x 255mm(D)		
PACKAGED DIMENSIONS	555(H) x 560(W) x 180mm(D)		