




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Dust Cover**

Primary Product Material: **PVC**

Operating Temperature (Max): **125 °C [ 257 °F ]**

Operating Temperature Range: **-65 – 125 °C [ -85 – 257 °F ]**

Features

Product Type Features

Connector Cover Type	Dust Cover
----------------------	------------

Body Features

Primary Product Material	PVC
--------------------------	-----

Usage Conditions

Compatible With Connector Style	Receptacle
Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #3-1617108-4

[PRMAC-26Y= PRMA COTS TO-5 RELA](#)



TE Part #582501-1

[KEYING PLUG,AMP LEAF](#)

Documents

Product Drawings

[DUST CAP, RECP, AD](#)

English

CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_204131-1\\_F.2d\\_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_204131-1\\_F.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_204131-1\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1308940\\_Sec4\\_arinc600](#)

English



ARINC 600 Next Generation Receptacle Connector

English