




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **1 – 2.5 mm²**

Mating Tab Width: **2.8 mm [.11 in]**

Mating Tab Thickness: **.8 mm [.031 in]**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.8 mm[.031 in]
Terminal Orientation	Straight
Terminal Plating Material	Silver
Crimp Type	F-Crimp

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Locking Lance Height	1.2 mm[.05 in]
Wire Insulation Support	With

Dimensions

--	--

Product Length	21.1 mm[.83 in]
Compatible Insulation Diameter Range	1.8 – 2.9 mm[.071 – .144 in]
Terminal Material Thickness	.38 mm[.015 in]
Wire Size	1 – 2.5 mm ²

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	4000
Packaging Method	Box

Other

Line	FASTON .110
------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | FASTIN-FASTON 110




Automotive Housings(6)



Automotive Signal & Power Connector Housings(6)



Automotive Terminals(5)



Crimp Terminal Housings(34)




Insertion & Extraction Tools(3)



Quick Disconnects(78)


Customers Also Bought




TE Part #CC2643-000
B-106-7502CS100




TE Part #CC2637-000
B-106-1802CS100




TE Part #CC2621-000
B-106-1501CS100




TE Part #CC2649-000
B-106-1803CS50




TE Part #CC2631-000
B-106-7401CS100




TE Part #CC2641-000
B-106-3632CS100




TE Part #CC2645-000
D-406-0003CS50



TE Part #CC2630-000
B-106-4631CS100



TE Part #CC2644-000
B-106-8502CS100



TE Part #CC2628-000
B-106-3631CS100



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_928996-1_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_928996-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_928996-1_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English