

6ES7355-0VH10-0AE0 SIMATIC S7-300, CONTROL MODULE

Technical / CAx data



SIMATIC S7-300, CONTROL MODULE FM 355 C, 4 CHANNELS, CONTIN. 4 AI + 8 DI + 4 AO INCL. MULTI-LANG CONFIG. PACK., MANUAL AND GETTING STARTED (GER/EN/FR/IT) ON CD-ROM

General information

Consisting of MLFB

SWR:6ES73550VH100AE0_01;
SWR:6ES73550VH100AE0_02;
SWR:6ES73550VH100AE0_03;
SWR:6ES73550VH100AE0_04;
SWR:6ES73550VH100AE0_05;
SWR:6ES73550VH100AE0_06;
SWR:6ES73550VH100AE0_07;

Supply voltage

Load voltage L+

Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V

Input current

from load voltage L+ (without load), max.	310 mA; Typ. 260 mA
from backplane bus 5 V DC, max.	75 mA; typ. 50 mA

Power losses

Power loss, typ.	6.5 W
Power loss, max.	7.8 W

Digital inputs

Number/binary inputs	8
Input characteristic curve acc. to IEC 61131, Type 2	Yes

Input voltage

Rated value, DC	24 V
for signal "0"	-3 to +5 V
for signal "1"	13 to 30 V

Input current

for signal "1", typ.	7 mA
Cable length	
Cable length, shielded, max.	1000 m
Cable length unshielded, max.	600 m
Analog inputs	
Number of analog inputs	4
permissible input voltage for voltage input (destruction limit), max.	30 V
permissible input current for current input (destruction limit), max.	40 mA
Input ranges	
Voltage	Yes
Current	Yes
Thermocouple	Yes
Resistance thermometer	Yes
Input ranges (rated values), voltages	
0 to +10 V	Yes
Input resistance (0 to 10 V)	100 k Ω
-1.75 to +11.75 V	Yes
Input resistance (-1.75 to +11.75 V)	100 k Ω
-80 mV to +80 mV	Yes
Input resistance (-80 mV to +80 mV)	10 M Ω
Input ranges (rated values), currents	
0 to 20 mA	Yes
Input resistance (0 to 20 mA)	50 Ω
0 to 23.5 mA	Yes
Input resistance (0 to 23.5 mA)	50 k Ω
-3.5 to +23.5 mA	Yes
Input resistance (-3.5 to +23.5 mA)	50 Ω
4 to 20 mA	Yes
Input resistance (4 to 20 mA)	50 k Ω
Input ranges (rated values), thermoelements	
Type B	Yes
Input resistance (Type B)	10 M Ω
Type J	Yes
Input resistance (type J)	10 M Ω
Type K	Yes
Input resistance (Type K)	10 M Ω
Type R	Yes
Input resistance (Type R)	10 M Ω
Type S	Yes
Input resistance (Type S)	10 M Ω
Input ranges (rated values), resistance thermometers	
Pt 100	Yes
Input resistance (Pt 100)	10 M Ω
Thermocouple (TC)	
for thermocouples	Type B, J, K, R, S
[nicht versorgt: TAK_ABT261_001_000]	
internal temperature compensation	Yes
external temperature compensation with Pt100	Yes
Resistance thermometer (RTD)	
Characteristic linearization	
for resistance thermometer	Pt100 (standard)
Characteristic linearization	
Parameterizable	Yes
Cable length	
Cable length, shielded, max.	200 m; 50 m at 80 mV and thermocouples

Analog outputs	
Number of analog outputs	4
Voltage output, short-circuit protection	Yes
Voltage output, short-circuit current, max.	25 mA
Current output, no-load voltage, max.	18 V
Output ranges, voltage	
0 to 10 V	Yes
-10 to +10 V	Yes
Output ranges, current	
0 to 20 mA	Yes
4 to 20 mA	Yes
Connection of actuators	
for voltage output 2-conductor connection	Yes
for current output 2-conductor connection	Yes
Load impedance (in rated range of output)	
with voltage outputs, min.	1 k Ω
with voltage outputs, capacitive load, max.	1 μ F
with current outputs, max.	500 Ω
with current outputs, inductive load, max.	1 mH
Cable length	
Cable length, shielded, max.	200 m; 50 m at 80 mV and thermocouples
Analog value creation	
Measurement principle	integrating
Integrations and conversion time/ resolution per channel	
Resolution with overrange (bit including sign), max.	14 bit; 12 or 14 bit, parameterizable
Conversion time (per channel)	16.67 ms; for 12 bit: 16 2/3 ms for 60 Hz, 20 ms for 50 Hz; for 14 bit: 100 ms for 50 and 60 Hz
Settling time	
for resistive load	0.2 ms
for capacitive load	3.3 ms
for inductive load	0.5 ms
Encoder	
Connection of signal encoders	
for voltage measurement	Yes
for current measurement as 4-wire transducer	Yes
Connectable encoders	
2-wire sensor	Yes
Permissible quiescent current (2-wire sensor), max.	1.5 mA
Errors/accuracies	
Linearity error (relative to input area)	+/- 0,05 %
Temperature error (relative to input area)	+/- 0,005 %/K
Linearity error (relative to output area)	+/- 0,05 %
Temperature error (relative to output area)	+/- 0,02 %/K
Operational limit in overall temperature range	
Voltage, relative to input area	+/- 0,6 %; +/-0.6 to +/-1%
Current, relative to input area	+/- 0,6 %; +/-0.6 to +/-1%
Resistance-type thermometer, relative to input area	+/- 0,6 %; +/-0.6 to +/-1%
Voltage, relative to output area	+/- 0,5 %
Current, relative to output area	+/- 0,6 %
Basic error limit (operational limit at 25 °C)	
Voltage, relative to input area	+/- 0,4 %; 80 mV: +/-0.6%; 250 to 1000 mV: +/-0.4%; 2.5 to 10 V: +/-0.6%; 3.2 to 20 mA: +/-0.5%
Current, relative to input area	+/- 0,4 %; +/-0.4 to +/-0.6 %
Resistance-type thermometer, relative to input area	+/- 0,4 %; +/-0.4 to +/-0.6 %
Voltage, relative to output area	+/- 0,3 %
Current, relative to output area	+/- 0,5 %

Interference voltage suppression for $f = n \times (f_l \pm 1\%)$, f_l = interference frequency	
Series mode interference (peak value of interference < rated value of input range), min.	40 dB
common mode voltage (USS < 2.5 V) , min.	70 dB
Interrupts/diagnostics/status information	
Substitute values connectable	Yes; Parameterizable
Control technology	
Number of closed-loop controllers	4
Galvanic isolation	
Galvanic isolation controller	
between the channels	No
between the channels and the backplane bus	Yes; Optocoupler
Permissible potential difference	
between inputs and MANA (UCM)	2.5 V DC
between M internally and the inputs	75 VDC / 60 VAC
Isolation	
Isolation checked with	500 V DC
Connection method	
required front connector	2x 20-pin
Dimensions	
Width	80 mm
Height	125 mm
Depth	120 mm
Weight	
Weight, approx.	470 g
Status	Apr 9, 2012