

## FEATURES

- Thread-cutting self-tapping screws with pan and countersunk heads
- A2 stainless steel
- Generally non-magnetic
- Cannot be hardened by heat treatment
- Supplied in a polypropylene case with a hinged cover

## 890 piece Stainless Steel Screw/Bolt Kit, No. 10, No. 6, No. 8

RS Stock No.: 180-796



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From the trusted RS PRO brand, this set of high-quality cross-recess pan and countersunk head self-tapping screws are ideal for many applications. Self-tapping screws are split into two main categories, thread-forming and thread-cutting. The screws are similar in the job they do, however, they have two noticeable differences. One of the screws has a flat base, the other has a sharp point. The difference between self-tapping and self-drilling fasteners is that self-tapping screws will tap a hole into a soft material, self-drilling screws can drill a hole into anything from metal to wood meaning no pilot hole is needed.

### General Specifications

<b>Number Of Pieces</b>	890
<b>Screw/Bolt Type</b>	Self Tapping Screw
<b>Head Shape</b>	Flat, Pan
<b>Drive Type</b>	Pozidriv
<b>Kit Contents</b>	890 Self Tapping Screws, Supplied in a Moulded Plastic Storage Case
<b>Applications</b>	Carpentry, Construction and roofing, DIY applications

### Mechanical Specifications

<b>Screw/Bolts Lengths</b>	9mm to 25mm
<b>Thread Size</b>	No. 10, No. 6, No. 8
<b>Material</b>	Stainless Steel
<b>Stainless Steel Type</b>	304, A2
<b>Finish</b>	Plain
<b>Screw/Bolt Length Longest</b>	25mm
<b>Screw/Bolt Length Shortest</b>	9mm
<b>Specification</b>	DIN 7981, DIN 7982

Kit Contents							
Head Type	Size	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty
<b>Cross-recess Pan &amp; Countersunk Head, Stainless Steel</b>							
Pan cross-recess	No.6	9	70	13	70	19	50
CSK cross-recess	No.6	9	70	13	70	19	50
Pan cross-recess	No.8	13	50	19	50	25	40
CSK cross-recess	No.8	13	50	19	50	25	40
Pan cross-recess	No.10	13	40	19	40	25	35
CSK cross-recess	No.10	13	40	19	40	25	35

