



## Main

Range of product	Pumptrol
Product or component type	Float switch
Device application	Closed tank
Device short name	9037H
Product specific application	Liquid level control
Electrical circuit type	Power circuit
Quantity per set	Set of 1
Type of packing	Individual

## Complementary

Product destination	For closed tank
Device mounting	Screw-in bushing
Cable entry number	2 conduit entries for 3/4"-14 NPT conforming to UL 508
Contacts type and composition	2 NC, snap action, DPST-DB, Form YY
Controlled fluid	Fresh water at specific gravity of 0.85 in or higher -18...121 °C Sea water at specific gravity of 0.85 in or higher -18...121 °C Hydraulic oil at specific gravity of 0.85 in or higher -18...121 °C Corrosive fluid at specific gravity of 0.85 in or higher -18...121 °C
Motor power kW	1.5 KW (2 hp) at 115 V AC, 1 phase 2.2 KW (3 hp) at 115 V AC, 3 phases 2.2 KW (3 hp) at 230 V AC, 1 phase 3.7 KW (5 hp) at 230 V AC, 3 phases 0.75 KW (1 hp) at 460 V AC, 3 phases 0.75 KW (1 hp) at 475 V AC, 3 phases 0.18 KW (0.25 hp) at 32 V DC 0.37 KW (0.5 hp) at 115 V DC 0.37 kW (0.5 hp) at 230 V DC
Electrical connection	Screw-clamp terminals, clamping capacity: 10 AWG
Contact operation	Contacts close on liquid rise
Float movement	3.75...7 in adjustable
Float position	Left
Float rod angle	90° (offset)
Short-circuit protection	20 A cartridge fuse, type gG
Local signalling	With external pointer
Materials in contact with fluid	Stainless steel 316 Yellow brass Viton Stainless steel 304 Cast iron
Enclosure material	Cast aluminium
Operating position	Vertical position only
Electrical durability	100 cycles, operating rate <60 cyc/mn
Mechanical durability	300 cycles
Terminal block type	4 terminals
Maximum operating rate	60 cyc/mn
[Ui] rated insulation voltage	575 V conforming to UL 508
Terminals description ISO n°1	Line-load-load-line

Factory modification	Without
Kit composition	Rod Float switch Float

## Environment

Standards	UL 508 CE
Ambient air temperature for operation	-30...93 °C
Ambient air temperature for storage	-30...93 °C
NEMA degree of protection	NEMA 4 conforming to UL 50
Product certifications	UL listed file E12158[RETURN]CSA file LR25490

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	48.387 cm
Package 1 Width	19.05 cm
Package 1 Length	122.903 cm
Package 1 Weight	4.99 kg

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

## Contractual warranty

Warranty	18 months
----------	-----------