


U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
		12.09.2012

Fast, secure and damage-free assembly  
 Shaped contact surface prevents the spanner from sliding off

**Info**

Assembly tool for SKINTOP® gland sizes up to M110 x 2

**Application range**

Special tools designed for metric SKINTOP® brass types

**Product features**

Assembly set manufactured from chromium-plated tool steel

The SKINMATIC® MH set consists of three special keys:

OK 16/20 mm (M12/M16)

OK 24/29 mm (M20/M25)

OK 36/45 mm (M32/M40)



**Remark**


Not subjected to RoHS directive.

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: LAPP_PRO1059EN.pdf	1 / 3
--------------------	------------------------------	-------



Part number	Width of flat surface (mm)	Brass gland sizes	Overall length (mm)	PU pieces (set)
SKINMATIC® MH-Set				
61791273	16/20, 24/29, 36/45	M 12, M 16, M 20, M 32, M 40	200 / 220 / 250	1
SKINMATIC® MH single wrench				
61791267	54	M 50		1
61791268	67	M 63		1
61791269	75	M 63 PLUS		1
61791286	95	M 75		1
61791287	115	M 90		1
61791288	135	M 110		1

U.I. Lapp GmbH	PRODUCT INFORMATION	
		12.09.2012



Product Management	Document: LAPP_PRO1059EN.pdf	3 / 3
--------------------	------------------------------	-------