

MAGNESIUM IMPACT WRENCH WITH LED - EXTRA COMPACT

943 PC2 1/2

PROMO



- Magnesium alloy casing: lightweight and powerful
- Aluminium motor housing
- Compact dimensions allow use in small spaces
- Removable LED unit rechargeable with USB cable (3.7V 180 mAh Li-Ion battery)
- Reversible model with double hammer mechanism
- 3 tightening torque settings, always maximum untightening power
- Inversion and adjustment by Aluminium lever
- Progressive trigger
- Rubber side bumpers
- Balanced weight for maximum comfort
- Soft-touch bi-material handle
- Silencer and air exhaust integrated in the handle
- Spare rotor blades (8 pieces): code 1004755-64

Strokes per minute	1400
Square drive (")	1/2
Reccomended air pressure (bar)	6,2
Air inlet (")	1/4
Torque in use (Nm min-Max)	200-270
Vibrations (m/s ²)	3,9
Average air consumption (l/min)	167
Sound power dB(A)	107 ±3
Max torque (Nm)	950
Free speed (rpm)	10000

Stanley Black & Decker Italia S.r.l.



Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo da parte di Stanley Black & Decker, Inc.
Capitale Sociale I.V. € 12.000.000

Ø internal hose (mm)	10
Sound level dB(A)	95 ±3
Bolt capacity	M16

Family details

Code	LxPxH mm	 Weight gr	 Quantity for packaging
U09430002	144x62x197	1,4	1

Stanley Black & Decker Italia S.r.l.

Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
 Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
 Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo da parte di Stanley Black & Decker, Inc.
 Capitale Sociale I.V. € 12.000.000