

Diligence EV Data Loggers



Five Data Loggers make up the Comark Diligence EV range.

High specification for the toughest of applications

Comark's Diligence EV range of data loggers provides a complete solution for the measurement of temperature, humidity or mA current.

The loggers are stand-alone, lightweight and small enough to be used almost anywhere that regular monitoring is required, reducing the need for manual checks and improving the accuracy of your information.

Use with EV Software to program logger tasks, download and analyse data, keeping permanent records to meet the requirements of industry regulations.

Features:

- **LCD screen** allows instant local checks on current readings and alarms
- **Large memory capacity with wraparound** for continual real-time and historic data collection - no forgotten readings, just log data and download
- **Alarm** indication lights instantly warn of potentially unsafe conditions allowing instant corrective action
- **Water and dustproof** sealed to IP67 standards for long life expectancy and accuracy
- **Lumberg connector** provides secure connection of a wide range of Comark probes - types K, T or thermistor
- **Battery life up to five years** enabling logging assignments over extended periods
- **Models with external probes** are ideal for monitoring fridges and freezers
- **Models with built in sensor** are suitable for chillers, storage and transport applications
- **Model measuring mA current** can be easily connected into the control loop and programmed to measure a wide range of parameters for process and building management checks such as pressure, pH, airflow, dissolved oxygen and many more
- **UKAS Calibration Certificates** available on all models

Comark is the leading manufacturer and supplier of a wide range of electronic measurement instruments for temperature, humidity, pressure and pH.

Click on www.comarkltd.com for more information

Diligence EV Data Loggers



TECHNICAL SPECIFICATIONS

Sensor Type N2011, N2012, N2013 N2014	Thermistor Type K or Type T Thermocouple
Measurement Range N2011, N2012 internal sensor N2012 external sensor N2103 Temperature Humidity N2014 Type K Type T Thermistor N2015	-40°C to +70°C / -40°F to +158°F -40°C to +150°C / -40°F to +302°F -20°C to +60°C / -4°F to +140°F 0 to 97% RH non condensing -200°C to +1372°C / -392°F to +2500°F -200°C to +400°C / -392°F to +752°F -40°C to +70°C / -40°F to +158°F 4 to 20mA
Scales Temperature Humidity	°C/°F RH or DP
Display Resolution Temperature Humidity N2015 only	0.1° (N2014 only, 1° below -100°C/-148°F and above +1000°C or °F) 0.1% RH 4 digits 1 decimal place (software allows 0 to 4 decimals in logged data*)
System Accuracy Temperature N2011, N2012, N2103 -25°C to +50°C / -13°F to +122°F -40°C to +80°C / -40°F to +176°F -40°C to +150°C / -40°F to +302°F Humidity N2013 -20°C to +60°C / -4°F to +140°F	±0.5°C/1°F ±1°C/2°F ±2°C/4°F (typical) ±3%
Instrument Accuracy At +20°C/+68°F ambient N2014 N2015	±0.5°C/±0.9°F +0.3% of reading ±0.3% of full scale
Memory 1 channel 2 channels 3 channels 4 channels 5 channels	32K 16000 samples 8000 samples 5300 samples 4000 samples 3200 samples
Logging Frequency	Programmable between 1 second and 99 hours
Communications	Via infrared interface

Download Time	3 minutes per 10,000 readings (typical)
Ambient Storage	-40°C to +70°C / -40°F to +158°F
Battery Type	1 x AA size 3.6V replaceable lithium battery
Battery Life	Up to 5 years
Case Material	ABS
Environmental Protection	IP67, EN 60529, IEC 529
LED Indication	Red = Alarm, Green = Logger Active

*Software selection of decimals will affect recorded values, e.g. selection of 0 decimals = a value of ±32000 and a selection of 4 decimals = a value of ±3.2000

DILIGENCE ACCESSORIES

EVSW	General use logger software
EVSWPRO	Professional version of logger software with security options to aid 21CFR Part 11 compliance
N2000CRU	USB Computer interface
N2000BOX	Multi-link box to connect up to four external sensors to N2012
N2000ADP/K	Adaptor cable to connect up to three Type K probes to N2014
N2000ADP/T	Adaptor cable to connect up to three Type T probes to N2014
ADP50	Adaptor cable to connect N2015 loggers to a sensor transmitter
SSF2	Stainless steel filter for N2013
A17476	Lithium battery with case seal

WARRANTY

All Comark instruments have a minimum one year warranty unless otherwise stated. The warranty period for temperature probes is for six months and all other probes and electrodes are unwarranted because the conditions of use are beyond our control.

The Comark warranty covers manufacturing defects and component failures on all products returned to Comark premises and applies worldwide. The warranty does not affect your statutory rights. In line with our policy of continuous development we reserve the right to alter any product specifications without notice.

All products are covered by our Quality Management System which is compliant with BS EN ISO 9001:2000 for the design, manufacture, supply, service, repair and recalibration of electronic measuring instruments and equipment.

Distributed by:

Comark Limited

Comark House, Gunns Wood Park,
Gunnels Wood Road, Stevenage,
Hertfordshire SG1 2TA England

Tel: 01438 (+44 1438) 367367
Fax: 01438 (+44 1438) 367400

Email: salesuk@comarkltd.com – UK and Ireland
salesint@comarkltd.com – International

Comark Instruments
PO Box 9090,
Everett, WA 98206, USA.

Tel: (503) 643 5204 Fax: (503) 644 5859
Email: sales@comarkUSA.com



CERTIFICATE No FM12129
ISO9001



0451



C183/1/EN © Comark Limited J42376/10/07

Click on www.comarkltd.com for more information