



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Primary Product Color: **Black**
Protection & Strain Relief Accessory Type: **Cover Assembly**
Primary Product Material: **PBT GF20**
Cable Exit Angle: **180°**
Strain Relief: **Without**

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Cover Assembly

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF20
Cable Exit Angle	180°

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	100 °C[212 °F]
Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]

Packaging Features

Packaging Method	Box
Packaging Quantity	250

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------





EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 8-1452423-2 %6 POS. PCM CPNNECTOR	 TE Part # 2-1564284-0 %6POS,MCON-1.2 CB,REC HSG,ASSY	 TE Part # 5-1564284-4 %6POS,MCON-1.2 CB,REC HSG,ASSY	 TE Part # 9-2359941-9 %6POS,MCON-1.2 CB,REC HSG,ASSY
 TE Part # 3-1564284-8 %6POS,MCON-1.2 CB,REC HSG,ASSY	 TE Part # 8-1452423-7 %6 POS. PCM CPNNECTOR	 TE Part # 3-1564284-7 %6POS,MCON-1.2 CB,REC HSG,ASSY	 TE Part # 6-1564284-5 %6POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 6-1564284-0
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 4-1564284-0
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 4-1564284-6
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 2359941-3
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 6-1452423-4
96 POS. PCM CPNNECTOR



TE Part # 2359941-4
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 6-1564284-1
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 8-1564284-1
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 6-1564284-3
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 2359941-1
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 4-1564284-7
96POS,MCON-1.2 CB,REC HSG,ASSY




TE Part # 9-1563173-4
96POS,MCON-1.2 CB,REC HSG,ASSY

Also in the Series | MCON 1.2mm




Automotive Connector Caps & Covers
(36)



Automotive Connector Locks & Position Assurance(15)



Automotive Housings(126)



Automotive Terminals(22)



Connector Seals & Cavity Plugs(8)



Insertion & Extraction Tools(31)




Other Automotive Connector Accessories(4)

Also in the Series | MCON Interconnection System




Automotive Connector Caps & Covers (36)



Automotive Connector Locks & Position Assurance(15)



Automotive Housings(126)




Automotive Terminals(22)



Connector Seals & Cavity Plugs(8)



Other Automotive Connector Accessories(4)




PCB Headers & Receptacles(3)



Rectangular Power Connectors(1)

Customers Also Bought



TE Part #144936-1
LOCKING DEVICE MQS



TE Part #K1060570
Relay 29-114-12




TE Part #3-640600-2
02P MTA156 CONN ASSY 20AWG LF



TE Part #1452388-1
2 LOCKING DEVI1.2



TE Part #9-1452415-9
58POS CONNECTOR ASSY F. CONNECTOR154POS




TE Part #963120-1
8P JUNIOR TIMER HOUSING




TE Part #185402-1
MODULAR RELAY HOLDER



TE Part #DTMH06-4SA
PLG, 4P, BLK, N, HI TEMP, A



TE Part #173850-2
070 MULTILOCK PLUG 8P



TE Part #2177472-1
73POS, MIXED,REC HSG,ASSY,BK

Documents



Product Drawings

COVER 96POS. ASSY

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1452862-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_1452862-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_1452862-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English