
Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20KBKO06EVX
COUPLING HALF: Coupler
BODY MATERIAL: Stainless Steel 316L
CONNECTION TYPE: Tube
FUNCTION: Double Shut-Off
CONNECTION SIZE: 4x6 MM

PRODUCT OVERVIEW

Parker’s Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:
- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

FOR FLUID TYPE	Water (Industrial, drinking, treated water)
WEIGHT	0.014 kg
BRAND	Rectus
APPLICATION	Energy Management
TECHNOLOGY	Fluid & Gas Handling
PLATING TYPE	Without Surface Treatment
INDUSTRY	Healthcare & Life Sciences
MAXIMUM OPERATING TEMPERATURE	392 °F
MAXIMUM OPERATING PRESSURE	507 psi
PRODUCT TYPE	Pneumatic Quick Couplings
REGION OF ORIGIN	Germany
INTERCHANGE TYPE	European Profile
MINIMUM OPERATING TEMPERATURE	5 °F
COMPATIBLE FITTING	Series 20 Plug
APPLICATION	Pharma
BODY MATERIAL	Stainless Steel 316L
PRODUCT SERIES	Series 20
BRAND	Parker
APPLICATION	Electronics
FUNCTION	Double Shut-Off
DIVISION	Low Pressure Connectors Europe Division

DIVISION	Low Pressure Connectors Europe Division
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
FLOW RATE	1.2 L/min (water)
CONNECTION SIZE	4x6 mm
APPLICATION	Industrial Machinery
VALVE INCLUDED	Yes
SLEEVE MATERIAL	Stainless Steel 316L
INDUSTRY	General Industrial
MINIMUM OPERATING TEMPERATURE	-15 °C
MAXIMUM OPERATING PRESSURE	35 bar
HEX SIZE	9 mm (external)
PRODUCT STYLE	Quick Connect
FOR FLUID TYPE	Chemicals (Paints, solvents, lubricants)
DIAMETER	2.7 mm (nominal)
MAXIMUM OPERATING TEMPERATURE	200 °C
APPLICATION	Food & Beverages
CONNECTION TYPE	Tube With hose nut, without spring guard
VALVE TYPE	Standard Valve
COUPLING HALF	Coupler
TECHNOLOGY	Pneumatics
FLOW RATE	130 L/min (air)
SEAL MATERIAL	FKM
QUANTITY PER BOX	2.0
OPERATION TYPE	Sleeve
APPLICATION	Medical

LENGTH	34 mm
INDUSTRY	Electronics