



— PRODUCT DATA SHEET

P5R



P5R



PRODUCT DESCRIPTION

Do you need a light to shine your way through the park at night or keep you company when you are working in the house or garden? The Ledlenser P5R is a strong option. The compact yet powerful torch has a focus function to adapt the light to each range and need. You can also use either rechargeable or disposable batteries and easily operate the torch with one button. Additionally, the high-quality housing is made of 75% recycled aluminium making the P5R a great environmentally friendlier option for the planet. Backed by a 7-year with registration warranty for complete peace of mind.

- Compact rechargeable torch with focus function (Advanced Focus System)
- Dual Power Source: Operates with rechargeable or disposable batteries, charging via USB-C (charging cable not included)
- Intuitive operation with one button
- Sustainable: Uses 75 % recycled aluminium⁹ and backed by a 7-year warranty*
- Element-proof: High water and dust resistance (IP68)

TECHNICAL DATA

| | |
|----------------------------|----------------|
| Weight incl. batteries [g] | 99 |
| Material | Aluminum alloy |
| Length [mm] | 121 |
| Length (focused) [mm] | 125 |
| Tube diameter [mm] | 22 |
| Head diameter [mm] | 30 |

POWER SUPPLY

| | |
|------------------------------|--|
| Battery quantity | 1 |
| Rechargeable | Yes |
| Battery type | Lithium-ion |
| Total battery voltage [V] | 3.7 |
| Total battery capacity [mAh] | 920 |
| Total battery energy [Wh] | 3.404 Wh |
| Battery replaceable | Yes |
| Charging time [min] | 180 |
| Useable batteries | Mignon (AA) 1.5V, AA NiMH 1.2V |
| Energy status indicator | Battery Indicator, Charge Indicator, Low Battery Warning |

FURTHER SPECIFICATIONS

| | |
|--------------------------------|------------|
| IP class | IP68 |
| Drop test (drop height) [m] | 2 |
| Working temperature range [°C] | -20 to +40 |

LIGHT FUNCTIONS

Cool White Main: Boost, Power, Mid power, Low power

LIGHT SOURCE

MAIN

| | |
|------------------------------|--------------|
| Amount LEDs | 1 |
| Colour | Cool White |
| Colour temperature [K] | 6000 to 7500 |
| Colour rendering index (CRI) | 70 |

LIGHT VALUES - Cool White Main

| | Boost | Power | Mid power | Low power |
|-------------------|-------|-------|-----------|-----------|
| Light output [lm] | 750 | 350 | 100 | 25 |
| Beam distance [m] | 280 | 180 | 100 | 50 |
| Run time [h] | - | 1 | 4 | 20 |

SWITCH

Front Switch

P5R

FEATURES

Transportation Lock

TECHNOLOGIES

Advanced Focus System, Temperature Control System, Flex Sealing Technology, Dual Power Source

P5R

PACKAGING AND LOGISTICS



For illustration purposes only

| PACKAGING INFORMATION | |
|---------------------------|---|
| Type of packaging | Box |
| Supplied with | Adjustable Lanyard, 14500 Li-ion rechargeable battery |
| Item No. | 503109 |
| Colour | Black |
| STERLING RRP inc / ex vat | £84.95 / £70.79 |
| EURO RRP inc / ex vat | €TBC / €TBC |
| SINGLE PACKAGE | |
| Dimensions W x H x D [cm] | 14.5 x 8.5 x 4.2 |
| Gross weight [g] | 171 |
| GTIN-13 | 4058205037310 |
| EXPORT CARTON | |
| Unit | 24 |
| Dimensions W x H x D [cm] | 37.5 x 17 x 31 |
| Gross weight [g] | 4760 |
| GTIN-13 | 4058205037297 |

P5R

PRODUCT SERIES

Powerful torches for those who push boundaries—the discerning enthusiasts, the industrious workers, the bold adventurers and the forward-thinkers. Lights that bridge the gap between the epic and the technical. In your hand, they do more than shine—they guide your path, reveal the unknown and empower you to explore, discover and redefine what is possible. Pioneering Brilliance. The P-Series: Redefined.

P5R

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

*) 7 year warranty only if registered, otherwise 2 years.
Warranty conditions viewable at <https://ledlenser.com/en/infos-service/warranty/>

1) Measured values according to ANSI/PLATO FL 1 in the respective setting named. If no setting is specifically named, the luminous flux (lumens/lm) and range (meters/m) values refer to the brightest setting and the burn time

(hours/h) values refer to the lowest setting. A boost function (if available) can be used several times, but is only available for a short time at a time. In case the lamp is equipped with colored LED(s), the measured values are given with white light or the white LED. If the lamp has different energy modes, the "energy saving mode" is the basis for the measurement.

2) Calculated value of the capacity in watt-hours (Wh). This applies to the battery(ies) contained in the delivery condition of the respective item or, in the case of lamps with rechargeable battery, to the battery(ies) contained herein in a fully charged condition.

9) All aluminium components are made of at least 75 % recycled aluminium and may thus vary in surface structure and color.