



DW331K

Jigsaw

- Powerful 701 Watt motor with variable speed delivers fast cutting action up to 3100 strokes per minute
- Quick and easy patented keyless blade change system accepts T- shank blades
- Patented anti-vibration counterbalance mechanism and rubber grip provide smooth operation

OVERVIEW

FEATURES

Powerful 701 Watt motor with variable speed delivers fast cutting action up to 3100 strokes per minute
Quick and easy patented keyless blade change system accepts T- shank blades
Patented anti-vibration counterbalance mechanism and rubber grip provide smooth operation
4-position pendulum action controls the aggressiveness or smoothness of cuts
Tool free adjustable shoe with anti scratch cover bevels to 45 degrees in both directions
Full wave electronic speed control with feedback ensures that blade speed is maintained under any load for a consistent finish across all materials
Soft start ensures accuracy at cut start
Tapered saw blade roller to control blade deflection at maximum depth of cut
Switchable dust blower keeps line of cut clear of chips
Modular component design for trouble free servicing
Compatible with DEWALT flush cutting blade DT2074, for cutting flush to an edge

STANDARD

Blade
Anti-scratch cover
Anti-splinter insert
Dust extraction adapter
Heavy duty carrying case

SPECIFICATIONS

Power Input	701 Watts
Power Output	445 Watts
No Load Stroke Rate	0-3100 spm
Stroke Length	26 mm
Bevel Capacity	45 °
Max. Cutting Capacity [Wood]	135 mm
Max. Cutting Capacity [Steel]	12 mm
Max. Cutting Capacity [Non Ferrous Metal]	30 mm
Hmotnost	2.8 kg
Length	250 mm
Height	210 mm
Hand/Arm Vibration - Wood	6.1 m/s ²
Uncertainty K 1 (Vibration)	2.0 m/s ²
Hand/Arm Vibration - Steel	4.9 m/s ²
Uncertainty K 2 (Vibration)	1.5 m/s ²
Sound Pressure	86.4 dB(A)
Uncertainty K 1 (Sound)	2.8 dB(A)
Accoustic Pressure	97.4 dB(A)
Uncertainty K 2 (Sound)	2.8 dB(A)