

Product data sheet

Subminiature connectors




Product description	M9 Male cable connector, Contacts: 8, 3.5-5.0 mm, shieldable, solder, IP67, with shielding cuff
Area	M9 IP67
Series	712
Part no.	99 0425 10 08


Illustration



Scale drawing



Contact arrangement (Plug-in side)



You can find the assembly instructions on the next page.

Technical data

General features

Part no.	99 0425 10 08
Connector design	Male cable connector
Version	Connector pin straight
Connector locking system	screw
Termination	solder
Degree of protection	IP67
Connection cross-section	max. 0.14 mm ² / AWG 26
Cable outlet	3.5-5.0 mm
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 500 Mating cycles
Weight (g)	18.45
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	125 V
Rated impulse voltage	1500 V
Rated current	1.0 A
Insulation resistance	≥ 10 ⁸ Ω
Pollution degree	1
Overvoltage category	II
Insulating material group	III
EMC compliance	shieldable
Shield connection	Shield cuff

Material

Classifications

Declarations of conformity

Trade-Compliance

Copper (9903.78.01)	0.000221 kg
---------------------	-------------

1. Kupplungshülse, Dichtung, Klemmkorb und Druckschraube auf Kabel aufhängen.

2. Kabel abmanteln auf $L = \text{min. } 10$ bis $\text{max. } 12 \text{ mm}$.

3. Litzen isolieren.

4. Schirm umlegen, Schirmmanschette an Kabeldurchmesser anpassen und mit Schirm verlöten. Überstehendes Geflecht abschneiden.

5. Litzen anlöten.

6. Kupplungshülse auf montierten Kontakteinsatz schrauben.

7. Druckschraube festziehen.

Technische Zeichnung: Montage eines Steckers in eine Hülse. Gezeigt werden die Komponenten: Kupplungshülse Stecker, Klemmkorb, Druckschraube, Dichttring, Kupplungshülse Dose, Buchseneinsatz, Steckereinsatz, Schirmmanschette, Gewinding Dose montiert, Gewinding Stecker montiert. Maßangaben: $0,8-1,0 \text{ Nm}$ für die Hülse, $0,2 \text{ Nm}$ für den Buchseneinsatz, $0,3-0,4 \text{ Nm}$ für die Druckschraube, $0,8-1,0 \text{ Nm}$ für den Steckereinsatz. Weitere Angaben: $\text{min. } 10$ abmanteln, $\text{max. } 12$, 3 , ~ 4 , ~ 4 , ~ 4 , ~ 4 .

Product description	M9 Male cable connector, Contacts: 8, 3.5-5.0 mm, shieldable, solder, IP67, with shielding cuff
Area	M9 IP67
Series	712
Part no.	99 0425 10 08

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".