

A-INL-PG16-N-S - Counter nut



1411260

<https://www.phoenixcontact.com/gb/products/1411260>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads Pg16, color: silver-colored



Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 1411260 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | AF7DZX |
| Product key | AF7DZX |
| Catalog page | Page 689 (C-2-2019) |
| GTIN | 4046356923927 |
| Weight per piece (including packing) | 4.77 g |
| Weight per piece (excluding packing) | 4.653 g |
| Customs tariff number | 74198090 |
| Country of origin | IN |

A-INL-PG16-N-S - Counter nut

1411260


<https://www.phoenixcontact.com/gb/products/1411260>

Technical data

Product properties

| | |
|--------------|----------|
| Product type | Flat nut |
| Thread type | Pg16 |

Dimensions

| | |
|-----------------------------|--|
| Dimensional drawing |  |
| Length | 3 mm |
| Diameter | 22.5 mm |
| Connecting thread diameter | 22.5 mm |
| Wrench size, counter nut | 26 mm |
| Hexagon angular dimension | 29 mm |
| Thread type connection side | Pg16 |

Material specifications

| | |
|----------|----------------------|
| Material | Brass, nickel-plated |
|----------|----------------------|

Cable/line

| | |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -70 °C ... 220 °C |
|---------------------------------|-------------------|

A-INL-PG16-N-S - Counter nut


1411260

<https://www.phoenixcontact.com/gb/products/1411260>



Drawings

Dimensional drawing



A-INL-PG16-N-S - Counter nut



1411260
<https://www.phoenixcontact.com/gb/products/1411260>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140807 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000879 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31161700 |
|-------------|----------|

A-INL-PG16-N-S - Counter nut



1411260

<https://www.phoenixcontact.com/gb/products/1411260>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 29f425b0-e6fe-45e7-932c-c510ac11d86d |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk