

LOC		DIST		REVISIONS					
F	LTR	DESCRIPTION				DATE	DWN	APVD	
	L	REVISED PER ECO-12-015521				28SEP12	KH	MZ	

D

C

B



A

D


C

B



A



DETAIL A



RECOMMENDED PANEL CUTOUT



DETAIL B

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2 WILL ACCEPT THIRTY-SEVEN (37) MULTIMATE SOCKET CONTACTS.
- 3 NO 4 FASTENER RECOMMENDED FOR MOUNTING.
- 4 NYLON 6/6, NATURAL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE 5	STANDARD	NO	3.81 [.150] DIA HOLE	A	4 206306-8
	SMALL PACK	NO	3.81 [.150] DIA HOLE	A	206306-6
	STANDARD	NO	4-40 THREADED INSERT	A	206306-5
	STANDARD	YES	-	B	206306-4
	STANDARD	YES	3.81 [.150] DIA HOLE	A	206306-3
	STANDARD	NO	-	B	206306-2
	STANDARD	NO	3.81 [.150] DIA HOLE	A	206306-1
	PACKAGING	PERIPHERAL SEAL	C	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.GELTZ 07/26/93	 TE Connectivity		
		CHK R.STONE 08/11/93			
DIMENSIONS: MM [INCHES]		APVD A.FRANTUM 08/13/93	NAME		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		RECEPTACLE HOUSING, REVERSE SEX, SHELL SIZE 23, CPC		
	0 PLC	±	PRODUCT SPEC 108-10024 APPLICATION SPEC		
	1 PLC	±			
	2 PLC	±			
	3 PLC	±			
4 PLC	±	SIZE			
5 PLC	±	CAGE CODE			
ANGLES	±	DRAWING NO			
FINISH	-	RESTRICTED TO			
MATERIAL: NYLON, BLACK INSERT: BRASS		WEIGHT	A1 00779  206306		
CUSTOMER DRAWING		SCALE			2:1
		SHEET			1 OF 1
		REV			L