



	Part Number	Thermal Resistance °C/W at 96in length	Width in	Height in	Surface Area in <sup>2</sup> in	Weight lb/ft	Part Class
	61715	0.29	6.50	1.60	43.2	2.80	C




**Thermal Curves**  
based on 96.000 in length


New Length   in  mm

**Natural Convection**

**Heat Sink Temperature Rise Above Ambient**




**Heat Sink Thermal Resistance**




# Forced Convection

Heat Sink Temperature Rise Above Ambient (100W Dissipated)



Heat Sink Thermal Resistance



# Building a Part Number

Full Bar Length = 8.00ft

Base Part #	Bar Length	Finish	Length (use zeros for full or half bars)
61715	1 Full	F Unfinished	0 0 0 0
	2 Half	F Unfinished	0 0 0 0
	3 Custom	B Black Anodized C Gold Chromate U Unfinished* V AavSHIELD <sup>3</sup>	<i>indicate length in inches to three decimal places; 1 5 2 5 0 = 15.250 "</i>

61715      \_      \_      \_ \_ \_ \_ \_

\*For unfinished extrusions with cut lengths other than half bar, the finish designation is a U.

Standard Aavid Thermalloy parts require all 12 positions to be complete.

# Non-Standard Extrusions

Aavid Thermalloy has over 10,000 extrusion profile designs on file, most with the extrusion die already available. These parts have minimum order requirements and longer lead times, but may be cost effective compared to a new design.

# Customizing & Advanced Capabilities

We offer several options for those applications which require a more unique solution. Challenge us with your thermal requirements - we can design custom solutions.