

Product datasheet

Specifications



APC Smart-UPS C, Line Interactive, 2000VA, Tower, 230V, 6x IEC C13+1x IEC C19 outlets, USB and Serial communication, AVR, Graphic LCD

SMC2000I

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 2 Weeks

Main

Product or component type	Uninterruptible power supply (UPS)
---------------------------	------------------------------------

Batteries & Runtime

Run Time	View Runtime Graph
Battery type	Lead-acid battery
Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	3...5 year(s)
Replacement battery	APCRBC148
Battery charger power	166 W rated

General

Provided equipment	CD with software Documentation CD USB cable
Number of power module	0
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Entry level
Redundant	No

Physical

Number of rack unit	0U
Colour	Black

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	21.6 cm
Width	17 cm
Depth	44 cm
Net weight	27.5 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Input Connection Type	IEC 320 C20
Input voltage limits	170...300 V adjustable 180...287 V
Network frequency	47...63 Hz

Output

Main Output Voltage	230 V
Rated power in W	1300 W
rated power in VA	2000 VA
output connection type	6 IEC 320 C13 1 IEC 320 C19
Harmonic distortion	Less than 5 % at full load
Maximum configurable power in VA	2000 VA
Maximum configurable power in W	1300 W
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50 Hz sync to mains

Conformance

Product certifications	C-Tick CE EAC GOST SABS VDE UK PSTI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	45 dBA
Heat dissipation	135 Btu/h

Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.0000000000...15240.0000000000 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

control panel	Multifunction LCD status and control console
Free slots	0
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rate	300 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33 cm
Package 1 Width	59 cm
Package 1 Length	37 cm
Package 1 Weight	30 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	2270
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Packaging	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	0637234b-27c7-4e32-ae29-543dd4803a99
REACH Regulation	REACH Declaration

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins