

CPF 0402 255R 0.1% 25PPM 1K RL

✓ ACTIVE

Neohm | Neohm CPF

TE Part # 9-1879213-0

TE Internal #: CPF0402B255RE1

[View on TE.com >](#)



Passive Components > Resistors > Fixed Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Size Code: **0402**

Packaging Method: **Taped & Reeled**

Tolerance: **.1%**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	25 V
Tolerance	.1%
Resistance Range	Up to 1kΩ Ω
Resistance	255 Ω
Power Rating	.063 W

Termination Features

Number of Terminations	2
Termination Type	Solder

Mechanical Attachment

Mount Style	Surface Mount
-------------	---------------

Dimensions

Dimensions	1 x .5 x .3 mm
------------	----------------

Usage Conditions



Temperature Coefficient	±25 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts





TE Part # 1879417-8
CPF0603 1M0 0.1% 25PPM
5K RL



TE Part # 1-1879417-9
CPF 0603 1M0 0.1%
25PPM 1K RL



TE Part # 1-1614959-4
CPF0805 2M0 0.1% 25PPM
1K RL



TE Part # 3-1879216-5
CPF0402 200K 0.1%
25PPM 1K RL

Also in the Series | Neohm CPF



Power Cable Assemblies(1)



Surface Mount Resistors
(3022)

Customers Also Bought



TE Part #1-2061980-0
FOSM GLARO LEAD 4.8
MM FXS MINI 10M



TE Part #5-1617794-0
PRMGSCD-6YW=.100
GRID DIODE RELAY



TE Part #7-1879213-9
CPF 0402 191R 0.1%
25PPM 1K RL



TE Part #2-1879214-0
CPF 0402 511R 0.1%
25PPM 1K RL



TE Part #4-1625868-9
RP 2A 0.25W 16R9 0.1%
25PPM 1K RL




TE Part #1622747-1
LR2 1% 3K9



TE Part #5146888-2
1FHP,84,30A/S,S,C,S10,
12,13,15



TE Part #534267-8
60 MODIV VRT DR OE 100
/125



TE Part #EF8559-000
R85049/88-17Z02



Documents

Product Drawings

CPF 0402 255R 0.1% 25PPM 1K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-1879213-0_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-1879213-0_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-1879213-0_BA.3d_stp.zip

English

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

CPF-1016

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

Product Environmental Compliance

TE Material Declaration

English