

SD UHS-I V30 (DDR200)

SD V30 Catalyst Series

Specifications

Capacity

- 64GB/128GB/256GB/512GB/1TB

Flash Type

- 3D TLC/QLC

Video Speed Class

- Up to V30

Bus Speed Mode

- Class 10
- UHS-I, U1/U3

Power Consumption Note

- UHS-I Mode
- Power Up Current < 250uA
- Standby Current < 1000uA
- Read Current < 400mA
- Write Current < 400mA

CPRM Optional (Content Protection for Recordable Media)

Advanced Flash Management

- ECC Correction
- Static and Dynamic Wear Leveling
- Bad Block Management

Write Protect with mechanical switch

- Supply Voltage
✓ 2.7V ~ 3.6V

Temperature Range

- Operating temperature: -25°C ~ 85°C
- Storage temperature: -40°C ~ 85°C

RoHS compliant

- FCC / CE / RoHS

EMI compliant

Warranty

- Lifetime-limited warranty ³

Table of Contents

Specifications	1
Product datasheet	3
1. Order information	3
2. Performance	3
3. Power Consumption	4
4. Physical Dimension Diagram	5
5. Compliance	6
Legal information	7
Limited Warranty Policy	7
Warranty Terms	7
Disclaimer of liability	7
Copyright notice	8
Contact information	8
Revision history	9

Product datasheet

1. Order information

PART NUMBER	CAPACITY*	FLASH TYPE	FORM FACTOR
EX64GSDU1	64GB *	3D TLC/QLC	SD UHS-I V30
EX128GSDU1	128GB *	3D TLC/QLC	SD UHS-I V30
EX256GSDU1	256GB *	3D TLC/QLC	SD UHS-I V30
EX512GSDU1	512GB *	3D TLC/QLC	SD UHS-I V30
EX1TSDU1	1TB *	3D TLC/QLC	SD UHS-I V30

2. Performance

	SD UHS-I V30 (Catalyst)				
Capacity	64GB	128GB	256GB	512GB	1TB
Burst Read (MB/s)	180	180	180	180	180
Burst Write (MB/s)	150	150	150	150	150
Form factor	SD UHS-I V30				

3. Power Consumption

Power Consumption of SD card (UHS-I Mode)

Bus Speed Mode		Max. Power Up	Max. Standby	Max. Read	Max. Write
		Current (uA)	Current (uA)	Current (mA)	Current (mA)
Default Speed Mode		250	1000	150 @ 3.6V	150 @ 3.6V
High Speed Mode		250	1000	200 @ 3.6V	200 @ 3.6V
UHS-I Mode	UHS50 / DDR50	250	1000	400 @ 3.6V	400 @ 3.6V
	UHS104 / DDR50	250	1000	400 @ 3.6V	400 @ 3.6V

*Power consumptions are measured at room temperature.

*For SDXC, up to 100mA from VDD1 when XPC=0; up to 150mA from VDD1 when XPC=1.

32mm(L)x24mm(W)x2.1mm(H)



5. Compliance

Exascend SD V30 memory card complies with the following specifications:

- FCC
- CE
- RoHS

Legal information

Limited Warranty Policy

Exascend Corporation ("Exascend") warrants that Exascend's product, in its original sealed packaging, will be free from defects in materials and workmanship. Subject to the conditions and limitations set forth below, Exascend will either repair or replace any part of its products that prove defective by reason of improper workmanship or materials. This warranty is non-transferable and valid only for the original purchaser of the Exascend products, except where prohibited by law. An original or copy sales receipt or invoice is required to establish purchase date and original purchaser.

1. This warranty supersedes all other warranties and representations, whether oral or written, between you and Exascend. Exascend makes no other warranties, including any warranty of merchantability or fitness for a particular purpose, whether expressly or implied.
2. All warranties, whether express or implied, are limited to the periods of time set forth below. Some states and jurisdictions do not allow such exclusion of implied warranties, limitations or warranty period, so above restrictions may not apply to you.
3. Exascend may acknowledge or read and save the data and information (collectively, "Information") stored in the product during after services. Exascend hereby agrees that Exascend will not disclose any Information to any third parties, except Exascend's employees, who may need to access the Information, with or without your prior written consent.

Warranty Terms

We offer limited-lifetime warranty for our SD cards.

The warranty period is the SHORTER OF:

- a period of lifetime beginning from the date of purchase; or

This Limited Warranty will not apply to, and Exascend will have no liability or obligation with respect to, problems or damage resulting from any of the following: (i) accident, modification, neglect, abuse, careless or incorrect handling, misuse or improper operation, disassembly, misapplication or use in unusual physical environments or under operating conditions not approved by Exascend (including, but not limited to, use of the Product with an improper voltage supply); (ii) normal wear and tear; (iii) removal of label(s) or sticker(s) provided on or with the Product (including all warranty or quality-control stickers, product serial or electronic numbers); (iv) problems relating to or residing in non-Exascend hardware, software or other items with which the Product is used; (v) use in an environment, in a manner or for a purpose for which the Product was not designed or not in accordance with Exascend's published documentation; (vi) installation, modification, alteration or repair by anyone other than Exascend or its authorized representatives; (vii) problems that do not relate to materials or workmanship or that have an insignificant impairment on the use or operation of the Product; or (viii) problems related to consumables; (ix) Product purchased "AS-IS" or "with known faults, defects or problems." Additionally, Exascend will have no liability or obligation to recover any data in the Product.

Disclaimer of liability

Exascend, Inc. reserves the right to make changes to specifications and product descriptions such as but not limited to numbers, parameters and other technical information contained herein without notice. Please contact Exascend, Inc. to obtain the latest specifications. Exascend, Inc. grants no warranty with respect to this datasheet, explicit or implied, and is not liable for direct or indirect damages. Some states do not grant the exclusion of incidental damages and as such this statement may not be valid in such states. The provisions of the datasheet do not convey to the purchaser of the device any license under any patent right or other intellectual property right of Exascend, Inc.

Customers must not use Exascend products in applications where a device failure or malfunction may cause personal injury or death, e.g., in life support systems or devices.

Exascend shall not be liable for any loss, injury or damage caused by use of the products in any of the following applications:

- Medical-related devices, life support, medical measurement devices, etc.
- Control devices for trains, ships, mass transportation systems or automotive vehicles, etc.
- Specific applications including military/defense-related equipment, aerospace, nuclear facility control systems, etc.
- Safety systems for disaster prevention/crime prevention, etc.

Copyright notice

Copyright © 2024 Exascend, Inc. All rights reserved. Information contained in this document, including but not limited to any instructions, descriptions, and product specifications, is considered proprietary and confidential to Exascend, Inc. and shall not be modified, used, copied, reproduced or disclosed in whole or in part, in any form or by any means, electronic or mechanical, for any purpose, without the written consent of Exascend, Inc.

Contact information

Exascend Taiwan Office

Address: Room 1, 6F, No.288, Sec. 6, Civic Blvd., Xinyi Dist., Taipei City 110, Taiwan (R.O.C.)

General Support: +886-2-2726-6500

Fax: +886-2-2726-6126

Email: sales@exascend.us

Revision history

Table 1: Catalyst SD V30 datasheet revision history

REVISION	DESCRIPTION	DATE
001	First released	Jul, 2021
002	Update Burst Speed	Feb, 2022
003	Add 256GB	May, 2022
004	Add 512GB	May, 2023
005	Add 1TB	May, 2023
006	Modify warranty	Sep, 2023
007	Modify temperature	Feb, 2024
008	Email updated	Jun, 2024
009	Format updated	Jun, 2024
010	Update storage temp.	Aug., 2024