



Figure similar

MOTION CONNECT 800PLUS

Article No. : 6FX8002-8QN21-1DE0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data

No. of cores x cross-section mm ²	4x2,5 + 4x0,2 + 2x1,5C C
Test voltage, rms Power conductors	1.5 kV
Test voltage, rms Signal conductors	0.5 kV
Type with braking lead	Yes
Rated voltage V0/V according to EN 50395	600 V/1000 V

Mechanical data

4x2,5 + 4x0,2 + 2x1,5C C	Type of connection cable engine side
Connector size	1 / M23
Type of bolting	not relevant
Type of connection cable converter side	Wire ends with ferrules (OCC signal connector pre-assembled)
Maximum cable outer diameter	13.6 mm
Length	34.0 m
Weight (without connector)	9.52 kg

Static deployment

Smallest bending radius (fixed installation)	39.9 mm
Tensile stress, max. Fixed installation	50 N/mm ² (7252 lbf/in ²)
Torsional stress	Absolute 30°/m

Dynamic deployment

Smallest bending radius (flexible installation in a cable carriers)	99.8 mm
Acceleration horizontal, max	50 m/s ²
Maximum traversing velocity	300 m/min
Travel path	50 m
Number of bends, max.	10,000,000
Tensile load for moving cable, max.	20 N/mm ² (2901 lbf/in ²)

Technical data

Ambient temperature

Operation with permanently installed cable	-20 ... 80 °C
	Module-end power connector 0 ... 55°C, Motor-end power connector -20 ... 80°C
Operation with moving cable	-20 ... 60 °C
	Module-end power connector 0 ... 55°C
Storage	-20 ... 80 °C
	Module-end power connector -20 ... 70°C, Motor-end power connector -20 ... 80°C

Kind of connection cable	Basis cable
Material of the cable sheath	PUR DESINA color orange RAL 2003
Type of insulation	CFC/halogen/silicone-free
Standard for behavior in fire: flame resistance	EN 60332-1-1 to 1-3
Oil resistance	EN 60811-2-1
Verification of suitability as authorisation for USA	UL 758
Verification of suitability as authorisation for Canada	CSA-C22.2-N.210.2-M90