

Technical data



1222SK

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, tapered bore, open

VISUAL (S)



1222SK

Double-row self-aligning ball bearings

PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	110 mm
D - External diameter	200 mm
B - Bearing/Inner ring width	38 mm
rs - Min fillet radius	2,1 mm
Associated sleeve reference	H222X
Radial clearance class	CN
Precision class	P0
Mass	5,21 kg

PRODUCT PERFORMANCE	
C - Dynamic load	87000000 mN
C0 - Static load	38500000 mN
Cu - Fatigue limit load	1500000 mN
e - Coefficient	0.18
Y0 - Static axial load coefficient	3.9
Y1 - Lower axial load coefficient	3.7
Y2 - Upper axial load coefficient	5.7
N lim - Oil lubrication limit speed	20400 °/s
N lim - Grease lubrication limit speed	16800 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT	
da min - Min shoulder diameter IR	121 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

1222SK

Double-row self-aligning ball bearings

ABUTMENT	
da max - Max shoulder diameter IR	138 mm
db - Min diameter for Sleeve	116 mm
Ce - Min length fro Sleeve	7 mm
Da max - Max shoulder diameter OR	189 mm
ra max - Max shaft & housing fillet radius	2 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15