

# BL82 - Filter/regulator – Lubricator Combination Units Excelon® Plus Modular System

- > Port size: 1/4" & 3/8" (ISO G/PTF)
- Unique Quikclamp connection system offers full modularity
- > 40 micron particle and high efficiency water removal (> 95%)
- Double safety lock on bowl
- > Integrated gauge
- Shut off valve, regulator and filter regulator with tamper resistance feature

- Metal bowl with prismatic liquid level indicator
- Light weight polycarbonate bowl
- Easy to read flush mounted integrated pressure gauge as standard
- All round (360°) visibility of sightdome for ease of drip rate setting





# **Technical features**

### Medium:

Compressed air only

# Maximum supply pressure:

Polycarbonate bowl: 10 bar (145 psi) Metal bowl: 17 bar (246 psi)

# Outlet pressure ranges: 0,3 ...10 bar (4 ... 145 psi)

Filter element:

### / C

40 μm **Port size:** 

G1/4, G3/8, 1/4 PTF, 3/8 PTF

### Gauge:

Integrated as standard

### Diaphragm Type:

Relieving

# Drain:

Manual or automatic Automatic drain operating conditions (float operated):
Bowl pressure required to close drain: > 0.35 bar (5 psi)
Bowl pressure required to open drain: ≤ 0.2 bar (2.9 psi)
Minimum air flow required to close drain: 1 dm³/s.

### Ambient/Media temperature:

-10 ... +60°C (+14 ... +140°F) Metal bowl:

-20 ... +65°C (-4 ... +149°F) Air supply must be dry enough to avoid ice formation at temperatures below +2°C (+35°F).

# Materials:

Body: Die cast aluminum Body covers: ABS Bonnet: Acetal

Valve: PP Transparent Bowl :

Polycarbonate with

Polypropylene Guard.
Metal Bowl: Die cast Zinc with
PA liquid level indicator lens
Filter element: sintered PP
Bowl 'o'- ring: Chloroprene

Elastomers: NBR

### Technical data BL82—standard models

Symbol	Port Size	Shutoff Valve	Drain	Lubricator Type	Weight (kg)	Model *1)
	G1/4	With	Manual	Microfog	1,30	BL82-221G
	G3/8	With	Manual	Microfog	1,30	BL82-321G
	G1/4	With	Auto	Microfog	0,90	BL82-201G
	G3/8	With	Auto	Microfog	0,90	BL82-301G
	G1/4	Without	Manual	Microfog	1,00	BL82-225G
	G3/8	Without	Manual	Microfog	1,00	BL82-225G
	G1/4	Without	Auto	Microfog	0,60	BL82-205G
	G3/8	Without	Auto	Microfog	0,60	BL82-305G

<sup>\*1)</sup> All models shown here are supplied with integrated gauge applicable for flow direction left to right.

With flow direction right to left please use the online configurator www.imi-precision.com/air-preparation-configurator or contact IMI Norgren

In addition to the standard box set units shown on this data sheet, further combinations can be configured using our online Air Preparation configurator:

www.imi-precision.com/air-preparation-configurator








# Option selector \*1)






<sup>\*1)</sup> All models shown here are applicable for flow direction left to right.

With flow direction right to left please use the online configurator


www.imi-precision.com/air-preparation-configurator or contact IMI Norgren

### Flow characteristics

Inlet pressure: 10 bar (145 psi) Range: 0.3 to 10 bar (4 to 145 psi) Port size: 1/4", 40 µm element



Inlet pressure: 10 bar (145 psi) Range: 0.3 to 10 bar (4 to 145 psi) Port size: 3/8", 40 µm element





### **Accessories**



















Pressure switch interface

0523109000000000

G1/4

block (18D pressure switch)












- \*1) Flanged version. For other pressure ranges, please see data sheet 5.11.001  $^{*}$ 2) For other pressure ranges, please see data sheet 5.11.385
- \*3) For connection please use Quikclamp 82 series and Hybrid-Quikclamp 84 series





















<sup>\*3)</sup> Max. pressure of silencers listed in this data sheet : 10 bar. For pressure higher than 10 bar please contact IMI Norgren




# Maintenance/Service



# Spare parts







# **Dimensions**


08/20


# Shut-off valve, Filter/regulator and Lubricator


Dimensions in mm Projection/First angle












# Minimum clearance for bowl removal





# **Dimensions**

# Filter/regulator and Lubricator

Dimensions in mm Projection/First angle










# Accessories

42


ဓ္ဌ

# Quikclamp® with wall bracket





# Quikclamp®







# Pressure sensing block







# Full flow porting block






# Porting block for 18D pressure switch





# 18D Pressure switch






### 18D Porting block and 18D assembled


# © Q Q 32 44 44 44

# Pipe adaptor








### Connector 84-82 Series



# 51D Pressure switch - digital







- Switch OUT 1, green LED
- 2 Switch OUT 2, red LED
- 3 Dustproof protector
- Dustproof protector
  Connector M12 x 1
- 5 Inlet port
- 6 Alternative inlet port G1/8 plugged
- Thread for mounting screw

# Warning

These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under »**Technical features/data**«.

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult Norgren Ltd.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.