

SCALANCE X308-2LD, managed plus IE switch, 2x 1000 Mbit/s SM SC, 1x 10/100/1000 Mbit/s, 7x 10/100 Mbit/s RJ45 ports, LED diagnostics, error signaling Contact with select/set button, PROFINET IO device, network management, Integrated redundancy manager, office features (RSTP, VLAN, IGMP,..) C-plug in scope of delivery



Figure similar

Product type designation	SCALANCE X308-2LD
Transfer rate	
Transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
Interfaces / for communication / Integrated	
Number of electrical connections	
• for network components or terminal equipment	8
Number of 10/100 Mbit/s RJ45 ports / Integrated	
• with securing collar	7
Number of 10/100/1000 Mbit/s RJ45 ports / Integrated	
• with securing collar	1
Number of 1000 Mbit/s SC ports	
• for single mode (LD)	2
Interfaces / other	
Number of electrical connections	
• for signaling contact	1

<ul style="list-style-type: none"> • for power supply 	1
<ul style="list-style-type: none"> • for redundant voltage supply 	2
Type of electrical connection	
<ul style="list-style-type: none"> • for signaling contact 	2-pole terminal block
<ul style="list-style-type: none"> • for power supply 	4-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> • C-PLUG 	Yes

Signal inputs/outputs

Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> • at DC / Rated value 	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> • at DC / maximum 	0.1 A

Supply voltage, current consumption, power loss

Type of voltage supply / redundant power supply unit	No
Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> • external 	24 V
<ul style="list-style-type: none"> • external / minimum 	18 V
<ul style="list-style-type: none"> • external / maximum 	32 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	F 3 A / 32 V
Consumed current / maximum	0.4 A
Power loss [W]	
<ul style="list-style-type: none"> • at DC / at 24 V 	9.6 W

Ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation 	-40 ... +60 °C
<ul style="list-style-type: none"> • during storage 	-40 ... +70 °C
<ul style="list-style-type: none"> • during transport 	-40 ... +70 °C
Relative humidity	
<ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP30

Design, dimensions and weights

Design	compact
Width	120 mm
Height	125 mm
Depth	123 mm
Net weight	1.4 kg
Mounting type	When used in shipbuilding, installation on a 35 mm standard mounting rail is not permitted.

• 19-inch installation	No
• 35 mm DIN rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	No

Product features, product functions, product components / general

Cascading in the case of a redundant ring / at reconfiguration time of $\sim 0.3\text{ s}$	100
Cascading in cases of star topology	any (depending only on signal propagation time)

Product functions / management, configuration, engineering

Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• RMON	Yes
• Port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
Product function / switch-managed	Yes
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	Yes
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

Product functions / Diagnostics

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes
• SysLog	Yes

Product functions / VLAN

Product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
Number of VLANs / maximum	255
Number of VLANs - dynamic / maximum	255
Protocol / is supported / GVRP	Yes

Product functions / DHCP

Product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes

Product functions / redundancy

Product function	
• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• Passive listening	Yes
Protocol / is supported	
• STP/RSTP	Yes

• STP	Yes
• RSTP	Yes
• MSTP	Yes
• RSTP big network support	Yes
• LACP	Yes

Product functions / Security

Product function	
• ACL - MAC-based	Yes
• ACL - port/MAC-based	Yes
• IEEE 802.1x (radius)	Yes
• Broadcast/Multicast/Unicast Limiter	Yes
• broadcast blocking	Yes
Protocol / is supported	
• SSH	Yes

Product functions / time

Product function	
• SICLOCK support	Yes
Protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	No

Standards, specifications, approvals

Standard	
• for FM	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
• for hazardous zone / from CSA and UL	UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4
• for emitted interference	EN 61000-6-4:2007 (Class A)
• for interference immunity	EN 61000-6-2:2005

Standards, specifications, approvals / CE

Certificate of suitability / CE marking	Yes
---	-----

Standards, specifications, approvals / other

Certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
• C-Tick	Yes
• Railway application in accordance with EN 50155	No
• KC approval	Yes

Standards, specifications, approvals / marine classification

Marine classification association

• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• DNV GL	Yes
• Korean Register of Shipping (KRS)	Yes
• Polski Rejestr Statkow (PRS)	Yes
• Royal Institution of Naval Architects (RINA)	No

Standards, specifications, approvals / Product conformity

MTBF	25 y
------	------

Further information / Internet-Links

Internet-Link

• to website: Selector SIMATIC NET SELECTION TOOL	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

Security information

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

12/16/2019