


SM2404



Magnetic-inductive flow meter

SMK21XGX50KG/US-100



Product characteristics				
Number of inputs and outputs	Number of analogue outputs: 2			
Measuring range	5...600 l/min	0.3...36 m³/h	80...9510 gph	1.3...158.5 gpm
Process connection	threaded connection Rc 2 internal thread DN50			
Application				
Special feature	Gold-plated contacts			
Application	empty pipe detection; for industrial applications			
Media	conductive liquids; water; hydrous media			
Note on media	conductivity: ≥ 20 µS/cm			
	viscosity: < 70 mm²/s (40 °C)			

SM2404



Magnetic-inductive flow meter

SMK21XGX50KG/US-100

Medium temperature	-10...90 °C		14...194 °F	
Pressure rating	16 bar	232 psi		1.6 MPa
Electrical data				
Operating voltage	[V]	18...32 DC; (to SELV/PELV)		
Current consumption	[mA]	< 150		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	5		
Measuring principle		magnetic-inductive		
Inputs / outputs				
Number of inputs and outputs	Number of analogue outputs: 2			
Outputs				
Total number of outputs	2			
Output signal	analogue signal			
Number of analogue outputs	2			
Analogue current output	[mA]	4...20; (≤ 22 mA; scalable)		
Max. load	[Ω]	500		
Measuring/setting range				
Measuring range	5...600 l/min	0.3...36 m³/h	80...9510 gph	1.3...158.5 gpm
Display range	-720...720 l/min	-43.2...43.2 m³/h	-11410...11410 gph	-190.2...190.2 gpm
Resolution	0.5 l/min	0.02 m³/h	5 gph	0.1 gpm
Analogue start point ASP	0...480 l/min	0...28.8 m³/h	0...7610 gph	0...126.8 gpm
Analogue end point AEP	120...600 l/min	7.2...36 m³/h	1900...9510 gph	31.7...158.5 gpm
Low flow cut-off LFC	< 15 l/min	< 0.9 m³/h	< 240 gph	< 4 gpm
In steps of	0.5 l/min	0.02 m³/h	5 gph	0.1 gpm
Measuring dynamics	1:120			
Temperature monitoring				
Measuring range	-20...80 °C		-4...176 °F	
Display range	-40...100 °C		-40...212 °F	
Resolution	0.2 °C		0.5 °F	
Analogue start point	-20...60 °C		-4...140 °F	
Analogue end point	0...80 °C		32...176 °F	
In steps of	0.2 °C		0.5 °F	
Accuracy / deviations				
Flow monitoring				
Accuracy (in the measuring range)	± (0,8 % MW + 0,5 % MEW)			
Repeatability	± 0,2% MEW			
Temperature monitoring				
Temperature drift	± 0,0333 °C / K; ± 0,0599 °F / K			
Accuracy	[K]	± 1 (25 °C; Q > 15 l/min) / ± 1 (77 °F; Q > 4 gpm)		
Response times				
Flow monitoring				
Response time	[s]	0.35; (dAP = 0)		
Damping process value dAP	[s]	0...5		

SM2404



Magnetic-inductive flow meter

SMK21XGX50KG/US-100

Temperature monitoring				
Dynamic response T05 / T09		[s]	T09 = 3 (Q > 15 l/min) / T09 = 3 (Q > 4 gpm)	
Software / programming				
Parameter setting options		display can be deactivated; Display unit; empty pipe detection		
Operating conditions				
Ambient temperature		-10...60 °C	14...140 °F	
Storage temperature		-25...80 °C	-13...176 °F	
Protection		IP 65; IP 67		
Tests / approvals				
EMC		DIN EN 60947-5-9		
CPA approval		model number		004MI
		accuracy class		-
		maximum allowable error		± 1,5 % FS
		Q (min)		0,3 m³/h
		Q (t)		-
		Q (max)		36 m³/h
		Medium temperature		-10...70 °C
		Medium temperature		14...158 °F
Shock resistance		DIN EN 60068-2-27		20 g (11 ms)
Vibration resistance		DIN EN 60068-2-6		5 g (10...2000 Hz)
MTTF		[years]	85	
UL approval		UL Approval no.		I009
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request		
Mechanical data				
Weight		[g]	2725	
Housing		rectangular		
Dimensions		[mm]	180 x 103 x 117	
Materials		stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEI; FKM; PBT-GF20; TPE-U		
Materials (wetted parts)		stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEEK; FKM		
Process connection		threaded connection Rc 2 internal thread DN50		
Displays / operating elements				
Display		Display unit		6 x LED, green (l/min, m³/h, gpm, gph, °C, °F
		function display		1 x LED, yellow (10³)
		measured values		alphanumeric display, 4-digit
		programming		alphanumeric display, 4-digit
Display unit		l/min; m³/h; gpm; gph; °C; °F		
Accessories				
Items supplied		Label		
Remarks				
Remarks		MW = measured value		
		MEW = Final value of the measuring range		
Pack quantity		1 pcs.		

SM2404



Magnetic-inductive flow meter

SMK21XGX50KG/US-100

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1: colours to DIN EN 60947-5-2
analogue output Temperature monitoring
OUT2: analogue output volumetric flow quantity monitoring
Core colours :
BK = black
BN = brown
BU = blue
WH = white


Magnetic-inductive flow meter

SMK21XGX50KG/US-100


Diagrams and graphs

Pressure loss

dP [mbar] DN50



dP [psi]



dP Pressure loss

Q volumetric flow quantity