

METAL CIRCULAR SAW 184 MM XR 18V

PERFORMING

- Cutting depth and power with brushless motor
- Clean cut to reduce the need for deburring
- Collect the chips as they are cut

PRACTICE

- Viewing windows with light for clear visibility of the blade
- Stainless steel sabot with measuring marks
- Optimized protection for better visibility of the blade
- Upper blade guard easy to remove to monitor the level of harvested chips

PRECISE

- Adjusting the cutting depth to fit any application
 - Adjusting the rear protection for irregular profiles and in diving
- ## ERGONOMIC for maximum control
- Balanced, light (magnesium parts)
 - Overmolded rear grip for maximum grip and increased control
 - Ergonomic front handle

SECURED

- Push lock button to prevent accidental starts
- Quick and easy blade change



Tension	18 V
Type de moteur	Moteur BL61x30
Diamètre de la lame	184 millimètre
Taille de l'arbre	20 millimètres
Vitesse à vide	3900 tr/min
Efficacité de la collecte des copeaux	75 % @ DOC complet
Poids (hors batterie)	4,8 kg



Delivered with a 48-tooth blade (TCT)

DCS383N-XJ	5 035 048 808 061
------------	-------------------

