

Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Plastik 70
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti Corrosion Products

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Laurinkatu 57 A 23 B, 08100 Lohja	+358/(19)32.921	+358/(19)383.676
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptongatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1
Extremely flammable aerosol.



Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname :	Plastik 70	Creationdate :	02.07.13 Version : 2.0
Ref.Nr.:	BDS000352_3_20130702	Replaces:	BDS000352_20130423

Health:	Pressurised container: May burst if heated. Eye irritation, category 2 Causes serious eye irritation. Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness.
Environment:	Not classified
Other hazards :	Repeated exposure may cause skin dryness or cracking.

Classification according to 67/548/EEC or 1999/45/EC:

Health:	R66: Repeated exposure may cause skin dryness or cracking. R67: Vapours may cause drowsiness and dizziness.
Physical:	EXTREMELY FLAMMABLE
Environment:	Not classified

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier:	Contains: n-butyl acetate ethyl acetate
----------------------------	---

Hazard pictogram(s):



Signal word:	Danger
---------------------	--------

Hazard statement(s):	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H319 : Causes serious eye irritation. H336 : May cause drowsiness or dizziness.
-----------------------------	---

Precautionary statement(s):	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.
------------------------------------	---

Supplemental Hazard information:	Repeated exposure may cause skin dryness or cracking.
---	---

2.3. Other hazards

None



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
n-butyl acetate	123-86-4	204-658-1	25-50		10-66-67	
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	25-50	F+	12	K,G
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	203-539-1	10-25		10-67	A
ethyl acetate	141-78-6	205-500-4	<20	F,Xi	11-36-66-67	B
Explanation notes						
A : substance with Community workplace exposure limit						
B : substance with national established workplace exposure limit						
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006						
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)						

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
n-butyl acetate	01-2119485493-29	123-86-4	204-658-1	25-50	Flam. Liq. 3, STOT SE 3	H226,H336	
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	-	68512-91-4	270-990-9	25-50	Press. Gas, Flam. Gas 1	H280,H220	K,G
1-methoxy-2-propanol; monopropylene glycol methyl ether	01-2119457435-35	107-98-2	203-539-1	10-25	Flam. Liq. 3, STOT SE 3	H226,H336	A
ethyl acetate		141-78-6	205-500-4	<20	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
Explanation notes							
A : substance with Community workplace exposure limit							
B : substance with national established workplace exposure limit							
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006							
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)							

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
 Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

Contact with skin :	If eye irritation persists: Get medical advice/attention. Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	Irritating to eyes Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO, CO₂

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources



Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.
Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Anti Corrosion Products

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :



Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
National established exposure limits, United Kingdom			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
hands and skin :	Wear suitable protective gloves against chemicals (polyvinylalcohol)
eyes :	Wear safety goggles.
Environmental protection:	Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state :	Propane/butane propelled liquid.
colour :	Colorless.
odour :	Solvent.
pH :	Not applicable.
Boiling point/range :	Not available.
Flash point :	< 0 °C (Closed Cup)
Evaporation rate :	Not available.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	Not available.
Relative density :	0.919 g/cm ³ (@ 20°C).



Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

Solubility in water : Insoluble in water
Auto-ignition : > 200 °C
Viscosity : Not available.

9.2. Other information

VOC: 700 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : May cause gastrointestinal disturbances
Skin contact : May cause irritation.
Eye contact : Irritating to eyes

Toxicological data :



Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LD50 oral rat	4016 mg/kg
		LC50 inhal.rat	27596 mg/l
		LD50 derm.rabit	2000 mg/kg
n-butyl acetate	123-86-4	LD50 oral rat	> 2000 mg/kg
		LC50 inhal.rat	> 20 mg/l
ethyl acetate	141-78-6	LD50 oral rat	5620 mg/kg
		LC50 inhal.rat	30 mg/l
		LD50 derm.rabit	> 20000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Not classified

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LC50 fish	6812 mg/l
		EC50 daphnia	23300 mg/l
n-butyl acetate	123-86-4	IC50 algae	647 mg/l
		LC50 fish	18 mg/l
		EC50 daphnia	44 mg/l
ethyl acetate	141-78-6	IC50 algae	5600 mg/l
		LC50 fish	230 mg/l
		EC50 daphnia	610 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available



Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203



Productname : Plastik 70
Ref.Nr.: BDS000352_3_20130702

Creationdate : 02.07.13 Version : 2.0
Replaces: BDS000352_20130423

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
EU-directive 99/45/EC
Regulation (EC) No 1272/2008 (CLP)
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R10: Flammable.
R11: Highly flammable.
R12: Extremely flammable.
R36: Irritating to eyes.
R66: Repeated exposure may cause skin dryness or cracking.
R67: Vapours may cause drowsiness and dizziness.

*Explanation hazard statements: H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.

REVISIONS IN CHAPTRE : 2.2. Label elements

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.