Photoelectrics Amplifier Type \$142A..





- µ-Processor controlled
- · Amplifier relay for photoelectric switches
- Automatic or manual emitter power regulation
- Self-diagnostic functions
- Alignment help
- Timer option, S142B..
- Rated operational voltage: 24 VAC/DC, 24 VAC, 115 VAC or 230 VAC
- Output 8 A/250 VAC SPDT relay and 100 mA NPN
- . LED indication: Automatic gain, output, level, emitter or receiver fault





Ordering Kev

S142 A RNN 924

u-Processor controlled amplifier for one set of photoelectric sensors, type MOFTR. Utilising an 11-pin plug for easy circular connection.

Product Description

8 A SPDT relay output, NPN / PNP transistor output or alarm output. Diagnostics for sensor test during operation. Alignment help via LED or alternation of alarm output. Level indication for dirt accumulation. Manual or automatic emitter power regulation. Two emitter codes available for high neighbour immunity.

<u> </u>	SITE A KINI /Z
Type	
Special function ————	
Output type ————	
(R-Relay, N-NPN, P-PNP, T	-Test)
Power supply	-

Type Selection

Function diameter	Ordering no.	Ordering no.	Ordering no.	Ordering no.
	Supply: 24 VAC/DC	Supply: 24 VAC	Supply: 115 VAC	Supply: 230 VAC
NPN output & Test input NPN output & Alarm output PNP out., PNP alarm & Test	S142 A RNT 924 S142 A RNN 924 ¹⁾ S142 A PPT 924	S142 A RNT 024 S142 A RNN 024 ¹⁾	S142 A RNT 115 S142 A RNN 115 ¹⁾ S142 A PPT 115	S142 A RNT 230 S142 A RNN 230 ¹⁾ S142 A PPT 230

¹⁾ Amplifier replacement for S1420156xxx

Specifications

Rated operational voltage (U _B) Pins 2 & 10 230 115 024 924	195 to 265 VAC, 45 to 65 Hz 98 to 132 VAC, 45 to 65 Hz 20.4 to 27.6 VAC, 45 to 65 Hz 20.4 to 27.6 VAC/DC Class 2	Output function Relay Transistor Alarm	Make or break on DIP-switch SPDT NPN / PNP, 100 mA, 40 VDC NPN / PNP, 100 mA, 40 VDC Delay on alarm 10 sec
Rated operational power		Test input (Mute)	NPN PNP
AC supply	3.3 VA	Emitter enabled	$> 5.0 \text{ VDC}$ $< V_{CC} - 3 \text{ VDC}$
AC/DC supply	1.6 VA / 1.4 W	Emitter disenabled	$< 3.0 \text{ VDC} > \text{V}_{\text{CC}} - 5 \text{ VDC}$
Delay on operate (t _v)	< 300 mS	Imax @ 40 VDC	1 mA
Outputs		Protection output	
Relay Rating (AgCdO)	μ (micro gap)	transistor	Reverse polarity, short circuit
Resistive loads AC1	8 A / 250 VAC (2500 VA)		and transients
DC1	0.2 A / 250 VDC (50 W)	Supply to sensors	
or	2 A 25 VDC (50 W)	Emitter	Pins 5 & 7
Electrical life (typical) AC1	> 100.000 operations	Supply voltage (open loop)	15 V square wave
Transistor output data		Current	< 450 mA, short circuit
Output current (I _e)	< 100 mA @ 40 VDC		protected
	(max. load capacity 100 nF)	Output resistance	10 Ω
Voltage drop (U _d)	< 2,5 VDC @ 100 mA	Receiver	Pins 6 & 8
		Supply voltage (open loop)	5 VDC
		Short-circuit current	10 mA
		Input resistance	470 Ω



Specifications

Emitter power Power Adjustment Manual Automatic /Auto LED ON)	Settings on DIP switch no 4, 50 % or 100 % range 240° Potentiometer Potentiometer settings to
	minimum
Sensing distance	Maximum range indicated on photoelectric switch datasheets in 100 % settings
Rated insulation voltage (U _I)	250 VAC
Dielectric voltage	>2.0 KVAC (rms) (contacts / electronics)
Rated impulse withstand volt.	4 kV (1.2/50 μS) (contacts / electronics) (IEC 664)
Operating frequency (f) Light / Dark ratio Relay output Transistor output	1:1 20 HZ 20 HZ

Response time OFF-ON (t_{ON}) ON-OFF (t_{OFF})	20 mS 30 mS
Environment Overvoltage categoty Degree of protection Pollution degree	III (IEC 60664) IP 20 /IEC 60529, 60947-1) 3 (IEC 60664/60664A, 60947-1)
Temperature Operating Storage	-20° to +50°C (-4° to +122°F) -50° to +85°C (-58° to +185°F)
Housing material	NORYL SE1, light grey
Weight AC supply AC/DC supply	200 g 125 g
Approvals	UL508, UL325, CSA
CE marking	EN12445, EN12453, EN12978

Specifications

Diagnostic

If a fault occurs on either the emitter or receiver the Alarm LED and output will turn ON.

Emitter fault

During normal operation the receiver is monitored for faults.

If the wires are short-circuited the "Code A, Yellow LED" flashes at a rate of 2 Hz. If the wires are broken the "Code A, Yellow LED" flashes at a rate of 4 Hz.

Receiver fault

During normal operation the emitter is monitored for faults.

If the wires are short-circuited the "Code B, Green LED" flashes at a rate of 2 Hz. If the wires are broken the "Code B, Green LED" flashes at a rate of 4 Hz.

Alignment

If the alignment DIP switch is set the Yellow Signal LED Flashes according to the signal quality.

Low frequency means weak signal.

Steady indication means maximum signal. On long distance it is not possible to get a steady signal but the alignment is optimal when the led flashes with the highest frequency.

On short distance the emitter power can be reduced using the potentiometer and then get better readings in the alignment LED.

The ALARM output will follow the Signal LED in align-


ment mode, so a Sensor tester (optional) can be connected to serve as a remote induction during alignment of the sensors.

NB! In alignment mode the output is off.

Code A or B

When two sensor pairs are mounted close to each other it is recommended to select one set to Code A and the other to Code B to avoid crosstalk.


Operation Diagram




²⁾ Switching function selected by DIP-switch, inverted function on pin 1, 4



Dimensions



Wiring Diagram



Connection to sensortester

Connection to sensortester ST-03 for alignment

	Sensortester		
	-	Signal	+
RNT Pin no.	10	9	
RNN Pin no.	10	11	
PPT Pin no.		9	2

Accessories

11 pole circular socket
Holding down spring
Mounting rack
Front panel mounting bezel

ZPD11
HF
SM13
FRS2

Delivery Contents

- Amplifier
- Packaging: Carton box