



ENGLISH

# Datasheet

## Multi-Purpose Foam Cleaner

RS Stock number [569-341](#)



### Description:

A solvent free aqueous based foam detergent cleaner designed to clean and degrease water and alkali resistant hard surfaces.

For use on all water and alkali resistant hard substrates, particularly on industrial applications. Use with care on glass. Failure to remove promptly may result in an etched effect.

Do NOT use on porous surfaces

Do NOT use on substrates believed to be adversely affected by alkaline products, without first ascertaining suitability for use on an inconspicuous area.



ENGLISH

### Benefits:

- Safer alternative to solvent based products
- Strong degreasing properties.
- Controlled rate of foam collapse.
- Suitable for use on horizontal and vertical surfaces.
- Removes grease, grime and general soiling.
- Foaming formula provides rapid penetration of soils.

### Physical Properties:

This is for the cleaner base except where stated.

Appearance:	Clear colourless liquid with a faint ammoniacal odour
pH:	12.0 ± 1.0
Specific Gravity:	1.020 ± 0.015
Non Volatiles % m/m:	1 – 5
Active Content % m/m, as supplied:	70 - 90
Viscosity at 20 °C:	Free flowing liquid
Flammability, as supplied:	Extremely flammable, flash point below -20°C
Composition Data, as supplied:	An aqueous solution of non-ionic and amphoteric surfactant, silicates, potassium hydroxide and ammonium hydroxide in butane/isobutane/propane propellant.
Service Temperature:	Designed for use at ambient temperatures

### Application Details:

Shake well before use. Ensure equipment is fully discharged before use. Spray apply from a distance of 20 – 30cm. Leave for a few moments for the foam to develop, and remove with a clean cloth. Ensure complete removal of all residues. Avoid overspray.

### Availability:

400 ml Aerosol