

PROSAFE

INDUSTRIAL LED FLASHLIGHTS

- » **PS-FL5** - 300 Lumen White Luxeon LED
- » **PS-FL7** - 500 Lumen White Cree LED
- » Industrial strength nylon-glass polymer body
- » Hard Anodized Die Cast Aluminium Head
- » 2 Light Mode Settings and 8Hz Defence Strobe
- » Tactical rubberised microswitch operation
- » IP67 total dust proof and 1m Submersible
- » AR Coated toughened glass lens
- » Impact resistant to 1m
- » Virtually indestructible

PS-FL5

BATTERY 4 x 1.5v AAA Duracell Alkaline batteries (inc)
WEIGHT 166g with batteries
DIMENSION 165 x 35mm

PS-FL7

BATTERY 4 x 1.5v AA Duracell Alkaline batteries (inc)
WEIGHT 291g with batteries
DIMENSION 188 x 43mm



1M SUBMERSIBLE



AR COATED TOUGHENED LENS



EXTRA RUBBERISED BODY



VIRTUALLY INDESTRUCTIBLE

UNILITE
PS-FL5

LIGHT BY
LUXEON



2¹/₂-12
HOURS
RUNTIME

170
METRE
BEAM RANGE

300
LUMENS
OUTPUT

IP67
DUST+WATER
PROOF

UNILITE
PS-FL7

LIGHT BY
CREE
LEDs



5-35
HOURS
RUNTIME

210
METRE
BEAM RANGE

500
LUMENS
OUTPUT

IP67
DUST+WATER
PROOF