


Geberit Mapress Stainless Steel flange PN 10/16, with plain end



Example image



CHARACTERISTICS

- Silicone-free (LABS-free)
- Design B1 (raised sealing strip with standard sealing strip), EN 1092-1

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

ACCESSORIES

- Geberit bolt set for flange connection, made of CrNi steel
- Geberit flange gasket, fibre composite material PN 10/16

| Art. no.                                                                                                     | DN  | d, ø<br>mm | di, ø<br>mm | D<br>cm | k<br>mm | m<br>mm | H<br>cm | h<br>cm | n<br>pc. | PN<br>bar |
|--------------------------------------------------------------------------------------------------------------|-----|------------|-------------|---------|---------|---------|---------|---------|----------|-----------|
| These articles are suitable for the following system: <b>Geberit Mapress Stainless Steel (silicone-free)</b> |     |            |             |         |         |         |         |         |          |           |
| 33748                                                                                                        | 50  | 54         | 51          | 16.5    | 125     | 18      | 11.3    | 1.8     | 4        | 10 / 16   |
| 33749                                                                                                        | 65  | 76.1       | 72          | 18.5    | 145     | 18      | 13.6    | 1.8     | 4        | 10 / 16   |
| 33750                                                                                                        | 80  | 88.9       | 84.8        | 20      | 160     | 18      | 15.2    | 2       | 8        | 10 / 16   |
| 33752                                                                                                        | 100 | 108        | 103.9       | 22      | 180     | 18      | 16.5    | 2       | 8        | 10 / 16   |

| Art. no.                                                                                                | DN  | d, ø<br>mm | di, ø<br>mm | D<br>cm | k<br>mm | m<br>mm | H<br>cm | h<br>cm | n<br>pc. | PN<br>bar |
|---------------------------------------------------------------------------------------------------------|-----|------------|-------------|---------|---------|---------|---------|---------|----------|-----------|
| These articles are suitable for the following system: <b>Geberit Mapress Stainless Steel (FKM blue)</b> |     |            |             |         |         |         |         |         |          |           |
| <b>33748</b>                                                                                            | 50  | 54         | 51          | 16.5    | 125     | 18      | 11.3    | 1.8     | 4        | 10 / 16   |
| <b>33749</b>                                                                                            | 65  | 76.1       | 72          | 18.5    | 145     | 18      | 13.6    | 1.8     | 4        | 10 / 16   |
| <b>33750</b>                                                                                            | 80  | 88.9       | 84.8        | 20      | 160     | 18      | 15.2    | 2       | 8        | 10 / 16   |
| <b>33752</b>                                                                                            | 100 | 108        | 103.9       | 22      | 180     | 18      | 16.5    | 2       | 8        | 10 / 16   |
| These articles are suitable for the following system: <b>Geberit Mapress Stainless Steel (gas)</b>      |     |            |             |         |         |         |         |         |          |           |
| <b>33748</b>                                                                                            | 50  | 54         | 51          | 16.5    | 125     | 18      | 11.3    | 1.8     | 4        | 10 / 16   |
| <b>33749</b>                                                                                            | 65  | 76.1       | 72          | 18.5    | 145     | 18      | 13.6    | 1.8     | 4        | 10 / 16   |
| <b>33750</b>                                                                                            | 80  | 88.9       | 84.8        | 20      | 160     | 18      | 15.2    | 2       | 8        | 10 / 16   |
| <b>33752</b>                                                                                            | 100 | 108        | 103.9       | 22      | 180     | 18      | 16.5    | 2       | 8        | 10 / 16   |
| These articles are suitable for the following system: <b>Geberit Mapress Stainless Steel</b>            |     |            |             |         |         |         |         |         |          |           |
| <b>33748</b>                                                                                            | 50  | 54         | 51          | 16.5    | 125     | 18      | 11.3    | 1.8     | 4        | 10 / 16   |
| <b>33749</b>                                                                                            | 65  | 76.1       | 72          | 18.5    | 145     | 18      | 13.6    | 1.8     | 4        | 10 / 16   |

| Art. no.                                                                           | DN  | d, ø<br>mm | d <sub>i</sub> , ø<br>mm | D<br>cm | k<br>mm | m<br>mm | H<br>cm | h<br>cm | n<br>pc. | PN<br>bar |
|------------------------------------------------------------------------------------|-----|------------|--------------------------|---------|---------|---------|---------|---------|----------|-----------|
| <b>33750</b>                                                                       | 80  | 88.9       | 84.8                     | 20      | 160     | 18      | 15.2    | 2       | 8        | 10 / 16   |
| <b>33752</b>                                                                       | 100 | 108        | 103.9                    | 22      | 180     | 18      | 16.5    | 2       | 8        | 10 / 16   |
| These articles are suitable for the following system: <b>Geberit Mapress Therm</b> |     |            |                          |         |         |         |         |         |          |           |
| <b>33748</b>                                                                       | 50  | 54         | 51                       | 16.5    | 125     | 18      | 11.3    | 1.8     | 4        | 10 / 16   |
| <b>33749</b>                                                                       | 65  | 76.1       | 72                       | 18.5    | 145     | 18      | 13.6    | 1.8     | 4        | 10 / 16   |
| <b>33750</b>                                                                       | 80  | 88.9       | 84.8                     | 20      | 160     | 18      | 15.2    | 2       | 8        | 10 / 16   |
| <b>33752</b>                                                                       | 100 | 108        | 103.9                    | 22      | 180     | 18      | 16.5    | 2       | 8        | 10 / 16   |