

Earth Auger XGT®

DG001G

40Vmax • 0 – 1 500 min⁻¹ • 55 / 136 Nm

XGT® battery powered brushless earth auger for drilling holes in the ground

DG001 is a powerful and lightweight brushless earth auger for drilling holes to the ground. Equipped with 2-speed options (0 - 400 min⁻¹ & 0 - 1 500 min⁻¹) and reverse. Max fastening torque (High / Low) is 55 / 136 Nm. Twin led lights illuminates the working area.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 400 / 1500 min ⁻¹
Max. Torque (2. Gear / 1. Gear)	55 / 136 Nm
Drill Chuck Capacity	2 - 13 mm
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Sound Power Level (L _{WA})	95 dB(A)
Sound Pressure Level (L _{pA})	87 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	842 x 605 x 199 mm
Tool weight with battery	7,2 - 8,1 kg

User benefits

- Brushless maintenance-free and long-life motor
- Variable 2-speed options allows the user to match speed to application
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Soft start for smooth start-ups
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.dk



Related products

Other

User manual

Parts drawing