



Brand of NTN corporation

Technical data



71908CVUJ84

High precision angular contact ball bearings



High precision angular contact ball bearing, laminated resin cage centred on outer ring

VISUAL (S)



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

71908CVUJ84

High precision angular contact ball bearings

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	40 mm
D - External diameter	62 mm
B - Bearing/Inner ring width	12 mm
d1 - External diameter inner ring	46,8 mm
D1 - Inner diameter outer ring	55,2 mm
D2 - Inner diameter outer ring	58,22 mm
a - Charge load application point	13 mm
- Contact angle	15 °
rs - Min fillet radius	0,6 mm
r1s - Min fillet radius	0,3 mm
Precision class	P4
Mass	0,11 kg

PRODUCT PERFORMANCE

C - Dynamic load	14300000 mN
C0 - Static load	11800000 mN
Cu - Fatigue limit load	650000 mN
f0 - Coefficient	15.906
Axial displacement K Factor	1.34
Preload level	8
Preload value	230000 mN
Axial rigidity	76 N/μm
Radial rigidity	368 N/μm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT PERFORMANCE

Tmin - Min operating temperature	243,15 °K
Tmax - Max operating temperature	393,15 °K
N lim - Oil lubrication limit speed	204000 °/s
N lim - Grease lubrication limit speed	138000 °/s

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	8.357 Hz
BPFI - Over rolling frequency on inner (60 rpm)	10.643 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	7.915 Hz
BRF - Rotational frequency - rolling element (60 rpm)	3.958 Hz
FTF - Rotational frequency - cage (60 rpm)	0.44 Hz

ABUTMENT

da min - Min shoulder diameter IR	44,5 mm
db min - Min IR shoulder diameter	44,5 mm
Da max - Max shoulder diameter OR	57,5 mm
Db max - Max OR shoulder diameter	57,5 mm
r1a - Max fillet radius	0,3 mm
ra max - Max shaft & housing fillet radius	0,6 mm



INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X \cdot Fr + Y \cdot Fa$$

Series			e	Single or DT bearing arrangement				DB or DF arrangement			
				Fa / Fr ≤ e		Fa / Fr > e		Fa / Fr ≤ e		Fa / Fr > e	
				X	Y	X	Y	X	Y	X	Y
70 (NTN & SNR) 72 (NTN & SNR) 78 (NTN) 79 (NTN) 719 (SNR)	15°	0.178	0.38	1	0	0.44	1.47	1	0.72	1.65	2.39
		0.357	0.4				1.4			1.57	2.28
		0.714	0.43				1.3			1.46	2.11
		1.07	0.46				1.23			1.38	2
		1.43	0.47				1.19			1.34	1.93
		2.14	0.5				1.12			1.26	1.82
		3.57	0.55				1.02			1.14	1.66
		5.35	0.56				1			1.12	1.63
	7.14	0.56	1	1.12	1.63						
	25°		0.68			0.41	0.87		0.92	0.67	1.41
30°		0.8			0.39	0.76		0.78	0.63	1.24	

Equivalent static radial load

$$P_0 = X_0 \cdot Fr + Y_0 \cdot Fa$$

Series			Single or DT bearing arrangement		DB or DF arrangement	
			X ₀	Y ₀	X ₀	Y ₀
70 (NTN & SNR) 72 (NTN & SNR) 78 (NTN) 79 (NTN) 719 (SNR)	15°		0.5	0.46	1	0.92
		25°		0.38		0.76
	30°			0.33		0.66

For single or DT bearing arrangement :

If $P_0 < Fr$, then use $P_0 = Fr$



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15