
Parker Product Datasheet



Coded industrial quick coupling system with nominal diameter 5 for pneumatic and fluid handling applications up to 35 bar. Coupling system developed on the basis of Parker Series 21. Available made of brass.

PART NUMBER: 21SFAW13MXX6
FUNCTION: Straight-Through
COLOR: Blue
COUPLING HALF: Plug
BODY MATERIAL: Brass
CONNECTION TYPE: Male BSPP
CONNECTION THREAD SIZE: G 1/4

PRODUCT OVERVIEW

Parker's Coded Quick Coupling Series 21 is an industrial coupling system developed on the basis of series 21 with above-average flow rate for liquid and gaseous media.
This coupling system is developed for single-hand operation. The mechanical coding of the coupling and plug offers a guarantee for avoiding mix-ups between media when coupling, which is complemented by the color coding of the anodized sleeves. A double shut-off version is available on request.

Markets:
- Machinery Construction
- Life Science
- Process
- Aerospace

Features/Benefits:
- No mix-ups between media due to the color and mechanical coding of coupling and plug
- Above-average flow rate
- Single-hand operation for easy and fast connection

Applications:
- Laboratory equipment
- Control panels
- Calibration systems
- Portable analyzers
- Gas chromatographs
- Micro-contamination devices

TECH SPECIFICATIONS

BODY MATERIAL	Brass
HEX SIZE	17 mm
DIVISION	Low Pressure Connectors Europe Division
CONNECTION SIZE	G 1/4
MAXIMUM OPERATING PRESSURE	12 bar
FLOW RATE	7 L/min (water)
SLEEVE MATERIAL	Without Sleeve
COMPATIBLE FITTING	Series 21 - Coded Coupler
FUNCTION	Straight-Through
DIVISION	Low Pressure Connectors Europe Division
BRAND	Rectus
MAXIMUM OPERATING TEMPERATURE	464 °F
PRODUCT TYPE	Pneumatic Quick Couplings
PRODUCT STYLE	Quick Connect
DIAMETER	5 mm (nominal)

MAXIMUM OPERATING TEMPERATURE	240 °C
TECHNOLOGY	Pneumatics
COUPLING HALF	Plug
INTERCHANGE TYPE	European Profile
SEAL MATERIAL	Without Seal
CONNECTION TYPE	BSPP
MAXIMUM OPERATING PRESSURE	174 psi
BRAND	Parker
MINIMUM OPERATING TEMPERATURE	-40 °C
CONNECTION TYPE	Male
REGION OF ORIGIN	Germany
APPLICATION	Food & Beverage
APPLICATION	Medical
VALVE INCLUDED	No
COLOR	Blue
QUANTITY PER BOX	5.0
INDUSTRY	Life Sciences
FOR FLUID TYPE	Water (Industrial, drinking, treated water)
OUTSIDE DIAMETER	n/a
PLATING TYPE	Without Surface Treatment
TECHNOLOGY	Fluid & Gas Handling
PRODUCT SERIES	Series 21 - Coded
APPLICATION	General industrial
OPERATION TYPE	No Sleeve
VALVE TYPE	No Valve

MINIMUM OPERATING TEMPERATURE	-40 °F
INDUSTRY	Industrial
LENGTH	41.5 mm
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
FLOW RATE	550 L/min (air)