

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable



1518311

<https://www.phoenixcontact.com/gb/products/1518311>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect eco, Type 2, Mobile AC charging cable, 32 A permanent, 480 V AC, with vehicle charging connector and infrastructure charging plug, Functional prototype, cable: 5 m, black, straight, with protective cap, with SAMPLE marking, PHOENIX CONTACT logo, IEC 62196-2, for charging electric vehicles (EV) with alternating current (AC), The protective cap included in the scope of delivery is plugged onto the vehicle charging connector for which protection is required by standard.

## Product description

Mobile AC charging cable with vehicle charging connector and infrastructure charging plug for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets, compatible with type 2 infrastructure charging sockets at charging stations for e-mobility (EVSE)

## Your advantages

- Complete product range
- Convenient handling due to the ergonomic, triple award-winning design
- Available with your logo on request - for consistent branding of your charging station
- Longitudinal water tightness reliably prevents water ingress
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Tested in accordance with automotive standards LV124, LV214, and LV215-2
- Tested in accordance with EV Ready 37 requirements
- Laser-marked mating face in accordance with DIN EN 17186

## Commercial data

Item number	1518311
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	XWBAEZ
Product key	XWBAEZ
GTIN	4063151980993
Weight per piece (including packing)	2,536 g
Weight per piece (excluding packing)	2,870 g
Customs tariff number	85444290
Country of origin	PL

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable



1518311

<https://www.phoenixcontact.com/gb/products/1518311>

## Technical data

### Notes

General	The protective cap included in the scope of delivery is plugged onto the vehicle charging connector for which protection is required by standard.
---------	---

### Product properties

Product type	AC charging cable
Product family	CHARX connect eco
Application	for charging electric vehicles (EV) with alternating current (AC) compatible with type 2 infrastructure charging sockets at charging stations for electromobility (EVSE)
Type	Mobile AC charging cable with vehicle charging connector and infrastructure charging plug Functional prototype
Design	with protective cap with SAMPLE marking
Affixed logo	PHOENIX CONTACT logo
Charging mode	Mode 3, Case B
Charging standard	Type 2
Customer variations	On request

### Electrical properties

Type of signal transmission	Pulse width modulation
Note on the connection method	Crimp connection, cannot be disconnected
Coding	220 $\Omega$ (between PE and PP)
Type of charging current	AC 3-phase
Charging power	26.6 kW (3-phase)
Charging current	32 A AC (3-phase)

#### Power contact

Number	5 (L1, L2, L3, N, PE)
Rated voltage	480 V AC
Rated current	32 A

#### Signal contact

Number	2 (CP, PP)
Rated voltage	30 V AC
Rated current	2 A

### Dimensions

#### Infrastructure charging plug

Width	57 mm
Height	77.5 mm

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable




1518311

<https://www.phoenixcontact.com/gb/products/1518311>

Depth	193.3 mm
-------	----------

## Vehicle charging connector

Dimensional drawing	
Width	70.4 mm
Height	82.3 mm
Depth	201.8 mm

## Material specifications

Color (Housing)	black (9005)
Color (Handle area)	black (9005)
Color (Mating face)	black (9005)
Color (Protective cap)	black (9005)
Color (Cable)	black (9005)
Material (Vehicle charging connector)	Plastic
Material (Cable outer sheath)	TPE-U
Material (Contact surface)	Silver

## Cable/line

Cable length	5 m
Wiring standards/regulations	prEN 50620/DIN EN 50620
Wiring certifications	VDE
Cable weight	max. 374.00 kg/km
Cable type	Class 5
Cable type	straight
Cable structure	5 x 4.0 mm <sup>2</sup> + 1 x 0.5 mm <sup>2</sup>
External cable diameter	14.20 mm ±0.3 mm
Outer sheath, material	TPE-U
Cable resistance	≤ 0.00425 Ω/m (based on a power core, at an ambient temperature of 20°C)
Bending radius	min. 113.6 mm (8x diameter)

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force	< 100 N
Withdrawal force	< 100 N

## Environmental and real-life conditions

### Ambient conditions

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable



1518311  
<https://www.phoenixcontact.com/gb/products/1518311>

Degree of protection (Vehicle charging connector)	IP44 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Infrastructure charging plug)	IP44 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Protective cap)	IP54
Ambient temperature (operation)	-40 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	max. 5000 m (above sea level)

## Standards and regulations

Standards	
Standards/regulations	IEC 62196-2

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable




1518311


<https://www.phoenixcontact.com/gb/products/1518311>

## Drawings

Dimensional drawing



Connection diagram



Pin assignment of Infrastructure Plug

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable


1518311

<https://www.phoenixcontact.com/gb/products/1518311>


Schematic diagram




[I]



[II]



[III]



[IV]



[V]


Operating instructions

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable

1518311


<https://www.phoenixcontact.com/gb/products/1518311>

Schematic diagram



Pin assignment of the Vehicle Connector

Schematic diagram



Terminology definition


# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable



1518311  
<https://www.phoenixcontact.com/gb/products/1518311>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1518311>

	<b>IECEE CB Scheme</b>			
	Approval ID: SG PSB-EH-00045			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	480 V	32 A	-	-

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable



1518311  
<https://www.phoenixcontact.com/gb/products/1518311>

## Classifications

### ECLASS

ECLASS-11.0	27144705
ECLASS-12.0	27144705
ECLASS-13.0	27144705

### ETIM

ETIM 9.0	EC002897
----------	----------

# CHARX ET2CP-3AC32-5,0MES00P1 - AC charging cable



1518311

<https://www.phoenixcontact.com/gb/products/1518311>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ff76bc08-b1a3-4dce-b590-f75848abc259

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)